



## Protect It! 6-Outlet Clamp-Mount Surge Protector, 6-ft. Cord, 2100 Joules, 2 x USB Charging ports (2.1A total)

MODEL NUMBER: TLP606DMUSB



### Highlights

- 6 outlet / 6-ft. cord
- 2100 joule rating
- 2.1 amp dual port USB charger
- Clamps to attach to desk, workbench or table

### Package Includes

- TLP606DMUSB surge suppressor
- Instruction manual with warranty information

### Description

Tripp Lite's TLP606DMUSB offers economical AC surge suppression for protection of workstations, desktop PCs, telecom systems and other sensitive electronics. Built-in AC surge suppression shields connected equipment from damage and performance problems due to transient surges. USB charging ports offer fast charging for smartphones, tablets, MP3 players and other portable devices.

TLP606DMUSB offers 6 total outlets, 6 foot cord, 2 USB charging ports and diagnostic LED to warn of suppressor damage. AC suppression rated at 2100 joules shields equipment from surges and line noise. This matte black surge suppressor has clamps that attach to the side of the desk, workbench or table. 2 knobs easily clamp to desk for better accessibility to plugs - 4 standard and 2 adapter spaced plugs.

\$40,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only).

PLUG/OUTLETS: Input: NEMA5-15P/Output: 6 NEMA5-15R/6-ft. AC line cord

ELECTRICAL: 120V AC, 50/60Hz, 15A (Requires NEMA5-15R wall receptacle)

FORMAT: Corded multi-outlet strip with 1 transformer spaced outlet

SUPPRESSION: AC: 150V RMS Clamping/2100 joules/400V UL1449 3rd Edition

### Features

- 6 outlets
- 6-ft. cord
- 2 USB charging ports - 2.1 amp total
- Surge suppression rating: 2100 joules
- Clamps for attaching to desk, workbench or table
- EMI/RFI noise filtering
- 15 amp resettable circuit breaker
- Green protection LED



- Includes full normal mode (H-N) and common mode (N-G/H-G) line surge suppression
- Can accommodate 2 large transformer plug without covering remaining outlets.
- 2 knobs to clamping to desk Lighted power switch
- \$40,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)
- Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required

## Specifications

OVERVIEW	
UPC Code	037332180292
Product Type	Surge Protector
Charging Form Factor	Strip
Device Compatibility	Phone; Tablet; Amazon Kindle
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Maximum Surge Amps	35500
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	6
Right-Angle Plug	No
Input Cord Length (m)	1.83
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(6) 5-15R
Circuit Breaker (amps)	15
Overload Protection	15A resettable illuminated combo switch / circuit breaker
Transformer Accommodation	(3) Yes
Outlet Orientation	Single row of 6 outlets
Right-Angle Outlets	No



<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Diagnostic LED(s)	Yes
Switches	Combination AC circuit breaker and 2 position red illuminated on/off power switch
Diagnostic LED Details	Built-in LED confirms suppressor "protection present" (green) status
<b>SURGE / NOISE SUPPRESSION</b>	
AC Suppression Joule Rating	2100
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping Voltage (RMS)	150
UL1449 Let Through Rating	400V
EMI / RFI Filtering	Yes
Automatic Shut-Off	Yes
<b>CHARGING</b>	
Charging Ports / Amps	(2) 2.1A
Number of Charging Ports	2
Charging Method	USB
Charging Port Type	USB A (FEMALE)
<b>DATALINE SURGE SUPPRESSION</b>	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
<b>PHYSICAL</b>	
Antimicrobial Coating	No
Color	Black
Color (AC Line Cord)	Black
Housing Color	Black
Integrated Keyhole Mounting Slots	No
Material of Construction	Plastic
Receptacle Color	Black
Shipping Dimensions (hwd / cm)	7.62 x 14.22 x 41.91
Shipping Dimensions (hwd / in.)	3.00 x 5.60 x 16.50
Shipping Weight (kg)	0.76



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Shipping Weight (lbs.)	1.68
<b>SPECIAL FEATURES</b>	
Rotatable Outlets	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Canada	cUL
Approvals	Exceeds IEEE 587 category A&B specifications
UL1449 3rd Edition (AC Suppression)	UL1449 3rd EDITION
UL1363 (Power Tap)	UL1363
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$40,000&nbsp;<a class="insuranceLink" href="//www.tripplite.com/support/insurance-policy">Ultimate Lifetime Insurance</a>&nbsp;

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>