

# Protect It! 6-Outlet Surge Protector, Right-Angle Plug, Side-Mount Switch, 1440 Joules, Tel/Modem Protection, 6 ft. (1.8 m) Cord, Black

MODEL NUMBER: TLP606SSTELB



Safeguard your workstation or home electronics against surges, spikes and line noise. Ideal for protecting your computer, printer, scanner, external hard drive, telecommunication devices and other sensitive electronics.

## Features

**1440-Joule Surge Protection for Home or Office Electronics** 1440-joule rating protects your computer, printer, scanner, external hard drive and other sensitive electronic components against even the strongest surges and spikes Backed by \$75,000 Ultimate Lifetime Insurance for any connected components damaged by power surge (U.S., Canada and Puerto Rico only) Full normal mode (H-N) and common mode (N-G/H-G) line surge suppression Filters out disruptive EMI/RFI line noise that can cause equipment damage or data loss Exceeds IEEE 587 Category A and B surge suppression specifications

**6 Outlets Accept Wide Range of Electronic Devices** 6 NEMA 5-15R AC outlets accept most computers and peripherals Special end outlet designed for bulky transformers without blocking other outlets Built-in RJ11 jacks provide surge protection for DSL or dial-up modem, fax or phone connections on single line

**Premium Safety Features** On/off switch mounted on side to prevent accidental shutoffs Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required Fail-safe thermal fusing protects against fire and other damage in case of extreme, extended overvoltage or surge

**Large LED Shows Protection Status** Clear acrylic edge lights up green to indicate your equipment is protected against surges Easy to see at a distance or in dark places Helps protect side-mounted on/off switch against accidental shutoffs

**Fits Effortlessly Into Your Workstation** Space-saving right-angle NEMA 5-15P plug on 6 ft. AC power cord allows furniture and equipment to move flush against the wall Keyhole slots on bottom panel provide convenient wall or desk mounting options Black plastic housing designed for long life

## Highlights

- 6 NEMA 5-15R outlets, including one for bulky transformers
- Surge suppression rating of 1440 joules
- Built-in RJ11 jacks protect modem, fax and phone connection
- Side-mounted on/off switch prevents accidental shutoff
- Large LED protection indicator easy to see from a distance

## Package Includes

- TLP606SSTELB Protect It! 6-Outlet Surge Protector
- Owner's manual

## Specifications

OVERVIEW	
UPC Code	037332190079



Powering Business Worldwide



<b>INPUT</b>	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Plug Features	Right Angle (90D)
Input Cord Gauge Type	14 gauge; SJT
Input Cord Gauge (AWG)	14
Voltage Compatibility (VAC)	120
Maximum Surge Amps	35500
Input Plug Type	NEMA 5-15P
Input Cord Details	SJT
Input Cord Length (ft.)	6
Right-Angle Plug	Yes
Input Cord Length (m)	1.83
Integrated Cord Clip	No
<b>OUTPUT</b>	
Frequency Compatibility	60 Hz
Output (Watts)	1800
Output Receptacles	(6) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(2) Yes
Outlet Orientation	Single row
Right-Angle Outlets	No
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Diagnostic LED(s)	Yes
Switches	Combination AC circuit breaker and 2 position red on/off power switch
Diagnostic LED Details	Built-in LED confirms suppressor "protection present" (green) status
<b>SURGE / NOISE SUPPRESSION</b>	
AC Suppression Joule Rating	1440
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
UL1449 Let Through Rating	400V
EMI / RFI Filtering	Yes
Automatic Shut-Off	Yes



Powering Business Worldwide



<b>DATALINE SURGE SUPPRESSION</b>	
Telephone/DSL Protection Details	1 line
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	Yes
<b>PHYSICAL</b>	
Material of Construction	Plastic
Power Cord Color	Black
Housing Color	Black
Mounting Holes or Slots	No
Slot or Hole Mount Measurement (Center to Center)	87 mm
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	12.99 x 3.94 x 1.50
Shipping Dimensions (hwd / cm)	32.99 x 10.01 x 3.81
Shipping Weight (lbs.)	1.28
Shipping Weight (kg)	0.58
Unit Dimensions (hwd / in.)	1.100 x 1.970 x 11.770
Unit Dimensions (hwd / cm)	2.79 x 5.00 x 29.90
Unit Weight (lbs.)	1.125
Unit Weight (kg)	0.51
Input Cord Color	Black
<b>FEATURES &amp; SPECIFICATIONS</b>	
Rotatable Outlets	No
Antimicrobial	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	CAN/CSA-C22.2 No. 269.3 (Canada); CAN/CSA-C22.2 No. 308 (Canada); cUL Listed; NOM (Mexico); UL 1449; UL 1363; UL Listed
Product Compliance	FCC Part 68; RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$75,000 <a class="insuranceLink" href="//tripplite.eaton.com/support/insurance-policy">Ultimate Lifetime Insurance</a>



*Powering Business Worldwide*



1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.