


Safe-IT 6-Outlet Surge Protector - 10 ft. Spiral Cord, 5-15P Plug, 300 Joules, Antimicrobial Protection, Black

MODEL NUMBER: TLP610COILAM



Surge protector with antimicrobial protection safeguards your valuable electronics against dangerous surges, spikes and line noise.

Features

6-Outlet Surge Protector Safeguards Your Sensitive Electronics

Ideal for your home, office, retail or industrial workstation, this Safe-IT™ surge protector features a 300 joule rating to defend your valuable electronic components against damaging power surges and spikes. The 10-foot (3-meter) coiled AC input cord with right-angle NEMA 5-15P plug gives you flexibility in placing the surge protector away from the nearest wall outlet.

NEMA 5-15R Outlets Accept a Wide Range of Electronic Devices

Plug your computer, printer, wireless router, desk lamp and other home/office electronics into six NEMA 5-15R outlets to protect them against dangerous surges, spikes and line noise.

Premium Protection from EMI/RFI Line Noise Helps Your Equipment Perform Better

This surge protector filters out disruptive EMI (electromagnetic interference) and RFI (radio frequency interference) line noise that can disturb your electronics and inflict hardware damage or data loss. This EMI/RFI filtering also helps your connected components perform better and last longer.

Includes the Latest Safety Features to Maintain Your Equipment's Well-Being

The lighted on/off switch allows easy one-touch control over equipment connected to the strip. An integrated 15-amp resettable circuit breaker helps prevent equipment damage due to overloads.

Antimicrobial Protection Helps Provide a Safer, Cleaner and Healthier Work Environment

The TLP610COILAM features antimicrobial protection that helps resist the growth of bacteria, viruses, fungi, mold and mildew.

Highlights

- 6 NEMA 5-15R outlets distribute AC power to connected home/office equipment
- 300 joules protect your valuable electronics against dangerous surges and spikes
- 10 ft. coiled input cord allows flexibility in placing devices away from wall outlet
- Lighted on/off switch gives you complete one-touch control over connected equipment
- Antimicrobial protection helps resist the growth of bacteria, viruses, fungi, mold and mildew

Package Includes

- TLP610COILAM 6-Outlet Surge Protector, Black
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332271907



Powering Business Worldwide



Product Type	Surge Protector
Charging Form Factor	Strip
Device Compatibility	Phone; Tablet; Amazon Kindle
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	10
Right-Angle Plug	No
Input Cord Length (m)	3.05
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	60 Hz
Output Receptacles	(6) 5-15R
Circuit Breaker (amps)	15
Overload Protection	15A resettable illuminated combo switch / circuit breaker
Transformer Accommodation	No
Outlet Orientation	Single row of 6 outlets
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	No
Switches	Combination AC circuit breaker
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	300
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
UL1449 Let Through Rating	500V all 3 lines
EMI / RFI Filtering	Yes
Automatic Shut-Off	No
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No



Powering Business Worldwide



Network (Ethernet) Protection	No
Telephone/DSL Protection	No
PHYSICAL	
Material of Construction	Plastic
Power Cord Color	Black
Housing Color	Black
Mounting Holes or Slots	Yes
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	4.13 x 12.00 x 4.13
Shipping Dimensions (hwd / cm)	10.49 x 30.48 x 10.49
Shipping Weight (lbs.)	2.98
Shipping Weight (kg)	1.35
Unit Dimensions (hwd / in.)	1.690 x 9.450 x 1.850
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	Yes
GaN Technology	No
Antibacterial	No
STANDARDS & COMPLIANCE	
Product Certifications	UL Listed; cUL Listed
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$10,000 Ultimate Lifetime Insurance

1000 Eaton Boulevard
 Cleveland, OH 44122
 United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
 Eaton is a registered trademark. All other trademarks
 are the property of their respective owners.