

## 7-Outlet -6 on strip/1 in detachable plug-Surge Protector, 2 USB Ports (2.4A Shared), Detachable Charger Plug, 6 ft. Cord, 5-15P Plug, 900 Joules, White

MODEL NUMBER: TLP616USB



Surge protector with detachable charger plug protects your electronic devices against dangerous surges, spikes and line noise.

### Features

#### 7-Outlet Surge Protector with USB Charging Safeguards Your Sensitive Electronics

Ideal for your home or office workstation or home theater, this Protect It!® seven-outlet surge protector features a surge suppression rating of 900 joules to defend your sensitive electronic components against even the strongest power surges and spikes. Because residential power outlets have three wires—hot line (H), neutral (N) and ground (G)—the TLP616USB protects all three, covering the two protection modes: full normal mode (H-N) and common mode (N-G/H-G).

#### Detachable Plug Provides Power and Charging at Home and on the Go

The six-foot braided cord and space-saving right-angle NEMA 5-15P plug allows you flexibility in placing the unit behind furniture or other tight places. Keyhole mounts on the rear allow for wall installation. For travel use, remove the plug to take a separate USB wall charger with you in your purse, briefcase or laptop bag. The detachable USB charger plug features one NEMA 5-15R outlet (without surge protection) and both USB ports.

#### NEMA 5-15R Outlets Accept a Wide Range of Electronic Devices

Plug your PC, printer, wireless router, game console, television, sound system or other home/office devices into the strip's six NEMA 5-15R outlets to protect them against dangerous surges, spikes and line noise.

#### 2 USB Ports Share 2.4 Amps of Charging Power

Two USB-A ports are available for charging your smartphone, tablet or other USB mobile devices. They share 2.4A for charging multiple devices at the same time.

#### Premium Protection from EMI/RFI Line Noise Helps Your Equipment Perform Better

Various electromagnetic and radio sources found in virtually every home and business can cause disruptive interference on the AC line. Known as EMI (electromagnetic interference) and RFI (radio frequency interference), this line noise is a common cause of performance problems. This surge protector filters out disruptive line noise that can disturb your electronics and inflict hardware damage or data loss. This EMI/RFI filtering also helps your connected components perform better and last longer.

#### Includes the Latest Safety Features to Maintain Your Equipment's Well-Being

The lighted on/off switch allows you easy one-touch control over equipment connected to the strip. An integrated 15-amp resettable circuit breaker helps prevent overloads. A green LED confirms your connected equipment is protected.

### Highlights

- Detachable plug provides a separate USB charger with included AC outlet
- 7 total NEMA 5-15R outlets - 6 on strip/1 on detachable plug - for powering computers, printers and other electronic devices
- 900 joules protect your valuable electronics against dangerous surges and spikes
- 2 USB ports share 2.4A for fast charging of phones, tablets and other mobile devices
- Right-angle NEMA 5-15P plug with braided 6 ft. cord allows connection in tight spaces

### Applications

- Protect a computer, router and other valuable electronics against AC power surges and spikes
- Detach the plug to carry a separate USB charger with AC outlet in your laptop bag, share power and charging in meeting or at home
- Filter potentially damaging line noise to improve connected equipment's performance and lifespan
- Safeguard valuable data against damage stemming from unexpected surges
- Charge a smartphone and tablet without taking up available AC outlets



#### Package Includes

- TLP616USB 7-Outlet Surge Protector, White
- Owner's manual

## Specifications

OVERVIEW	
UPC Code	037332260314
Product Type	Surge Protector
Charging Form Factor	Strip
Device Compatibility	Amazon Kindle; Headphones; Laptop; Phone; Tablet
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Input Cord Gauge Type	16 gauge
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	6
Right-Angle Plug	No
Input Cord Length (m)	1.83
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(2) 5-15/20R
Circuit Breaker (amps)	15
Overload Protection	15A resettable illuminated combo switch / circuit breaker
Transformer Accommodation	(2) Yes
Outlet Orientation	Single row of 6 outlets; 1 outlet in wall plug
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Diagnostic LED Details	Built-in LED confirms suppressor "protection present" (green) status



<b>SURGE / NOISE SUPPRESSION</b>	
AC Suppression Joule Rating	900
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
UL1449 Let Through Rating	L-N 700
EMI / RFI Filtering	Yes
Automatic Shut-Off	No
<b>CHARGING</b>	
Charging Ports / Amps	(2) 2.4A
Number of Charging Ports	2
Charging Method	USB
Charging Port Type	USB A (FEMALE)
<b>DATALINE SURGE SUPPRESSION</b>	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
<b>PHYSICAL</b>	
Color	White
Antimicrobial Coating	No
Color (AC Line Cord)	White and Gray
Housing Color	White
Integrated Keyhole Mounting Slots	Yes
Material of Construction	Plastic
Receptacle Color	Black
Unit Dimensions (hwd / cm)	26.4 x 5.3 x 3.3
Unit Dimensions (hwd / in.)	10.4 x 2.1 x 1.3
Unit Weight (kg)	0.56
Unit Weight (lbs.)	1.23
<b>SPECIAL FEATURES</b>	
Rotatable Outlets	No
<b>STANDARDS &amp; COMPLIANCE</b>	



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Canada	cUL
Approvals	EXCEEDS IEEE 587 CATAGORY A&B SPECIFICATIONS
UL1449 3rd Edition (AC Suppression)	UL 1449 4TH EDITION
UL1363 (Power Tap)	UL1363
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$5,000&nbsp;<a class="insuranceLink" href="//www.tripplite.com/support/insurance-policy">Ultimate Lifetime Insurance</a>&nbsp;

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>