

Protect It! Surge Suppressor - State of the art protection for every application

MODEL NUMBER: TLP61D



Highlights

- 6 safety outlet covers
- 2 m cord
- "Protected" LED
- 1140 joule rating

Package Includes

- TLP61D surge suppressor
- Instruction manual and warranty information

Description

Tripp Lite's Protect It!™ TLP61D offers economical AC surge suppression for full protection of 220-250V home computers, printers, scanners, and desk lamps. The TLP61D offers 6 Schuko type F outlets and a 2 meter AC line cord. Internal safety covers protect against accidental contact with unused outlets.

Features

- Protect It!™ TLP61D offers economical AC surge suppression
- 1140 joules AC surge suppression shields equipment from surges and line noise
- 6 Schuko outlets protects computers and peripherals
- 2 m cord with German plug
- Protected LED
- Internal safety covers protect against accidental contact with unused outlets

Specifications

OVERVIEW	
UPC Code	037332145451
INPUT	
Nominal Input Voltage(s) Supported	230V AC
Recommended Electrical Service	230V (220-250V)
Voltage Compatibility (VAC)	220-250
Input Plug Type	German
Input Cord Length (ft.)	6
Right-Angle Plug	Yes



Powering Business Worldwide



Input Cord Length (m)	1.83
Integrated Cord Clip	No
OUTPUT	
Circuit Breaker (amps)	10
Transformer Accommodation	(3) Yes
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Diagnostic LED Details	Green Protected
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	1140
Automatic Shut-Off	No
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
PHYSICAL	
Color	Light Gray
Power Cord Color	Light Gray
Housing Color	Light Gray
Mounting Holes or Slots	No
Receptacle Color	Light gray
Shipping Dimensions (hwd / in.)	17.10 x 4.53 x 2.17
Shipping Dimensions (hwd / cm)	43.43 x 11.51 x 5.51
Shipping Weight (lbs.)	1.30
Shipping Weight (kg)	0.59
Unit Dimensions (hwd / in.)	16.000 x 2.320 x 1.750
Unit Dimensions (hwd / cm)	40.64 x 5.89 x 4.45
Unit Weight (lbs.)	1.2
Unit Weight (kg)	0.54
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	No



Powering Business Worldwide



WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.