

## Protect It! 6-Outlet Surge Protector - 5-15R Outlets, 1500 Joules, 25 ft. (7.6 m) Braided Cord, Black

MODEL NUMBER: TLP625DB



Protects your home, office and small electronics against the harmful effects of surges, spikes and line noise.

### Features

#### 6-Outlet Surge Protector Safeguards Your Sensitive Electronics

Ideal for your home, office or retail workstation, this Protect It!® surge protector features a surge protection rating of 1500 joules to defend your valuable electronic components against power surges and spikes. Because residential power outlets have three wires—hot line (H), neutral (N) and ground (G)—the TLP625DB protects all three, covering the two protection modes: full normal mode (H-N) and common mode (N-G/H-G).

#### NEMA 5-15R Outlets Accept a Wide Range of Electronic Devices

Plug your computer, printer, router, desk lamp or other home/office electronics into six NEMA 5-15R outlets to protect them against dangerous surges, spikes and line noise. One outlet is placed at the end of the TLP625DB to allow connection of a bulky transformer without blocking adjacent outlets.

#### Premium Protection from EMI/RFI Line Noise Helps Your Equipment Perform Better

This surge protector filters out disruptive EMI (electromagnetic interference) and RFI (radio frequency interference) line noise that can disturb your electronics and inflict hardware damage or data loss. This EMI/RFI filtering also helps your connected components perform better and last longer.

#### Safety Features Help Maintain Your Equipment's Well-Being

A lighted on/off switch allows easy one-touch control over all equipment connected to the TLP625DB. An integrated 15A resettable circuit breaker helps prevent equipment damage by cutting power to outlets if the protection circuit is incapacitated. A diagnostic LED lets you know that your equipment is protected. The ABS plastic housing is fire-retardant to provide extra safety and durability.

#### Flexible Installation Options

Place the TLP625DB on any flat surface in your home, office, workbench or anywhere else you need power for your equipment. Integrated rear keyhole slots accommodate wall or desktop mounting. The 25-foot (7.6-meter) braided input cord with NEMA 5-15P right-angle plug allows you great flexibility in placing the surge suppressor away from the nearest wall outlet.

## Specifications

### Highlights

- 6 NEMA 5-15R outlets distribute AC power to connected home/office/work equipment
- 1500 joules protect your valuable electronics against dangerous surges and spikes
- 25 ft. braided input cord allows flexibility in placing devices away from wall outlet
- On/off switch with circuit breaker allows one-touch control over connected equipment
- Rear keyhole slots allow optional wall or desk mounting for convenient access

### Package Includes

- TLP625DB 6-Outlet Surge Protector
- Owner's manual



Powering Business Worldwide

TRIPP LITE  
SERIES

OVERVIEW	
UPC Code	037332291080
Product Type	Surge Protector
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Cord Gauge Type	14 gauge; SJT
Input Cord Gauge (AWG)	14
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Details	SJT
Input Cord Length (ft.)	25
Right-Angle Plug	Yes
Input Cord Length (m)	7.62
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(6) 5-15R
Circuit Breaker (amps)	15
Overload Protection	15A resettable illuminated combo switch / circuit breaker
Transformer Accommodation	(1) Yes
Outlet Orientation	Single row of 6 outlets
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Switches	Combination AC circuit breaker and 2 position red illuminated on/off power switch
Diagnostic LED Details	Built-in LED confirms suppressor "protection present" (green) status
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	1500
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
UL1449 Let Through Rating	500V



Powering Business Worldwide

TRIPP LITE  
SERIES

EMI / RFI Filtering	Yes
Automatic Shut-Off	Yes
<b>DATALINE SURGE SUPPRESSION</b>	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
<b>PHYSICAL</b>	
Material of Construction	Plastic
Power Cord Color	Black
Housing Color	Black
Mounting Holes or Slots	Yes
Slot or Hole Mount Measurement (Center to Center)	Distance between slots = 101 mm; Distance between slot height = 28 mm
Outlets Measurement (Center to Center)	28.5mm
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	15.70 x 2.20 x 6.10
Shipping Dimensions (hwd / cm)	39.88 x 5.59 x 15.49
Shipping Weight (lbs.)	2.50
Shipping Weight (kg)	1.13
Unit Dimensions (hwd / in.)	11.024 x 1.850 x 1.300
Unit Dimensions (hwd / cm)	11.024 x 1.85 x 1.299
Unit Weight (lbs.)	1.01
Unit Weight (kg)	0.46
<b>FEATURES &amp; SPECIFICATIONS</b>	
Rotatable Outlets	No
Antimicrobial	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	CAN/CSA-C22.2 No. 269.3 (Canada); CAN/CSA-C22.2 No. 308 (Canada); UL 1363; UL 1449
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$25,000 <a class="insuranceLink" href="//tripplite.eaton.com/support/insurance-policy">Ultimate Lifetime Insurance</a>



*Powering Business Worldwide*

TRIPP LITE  
SERIES

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.