

5-Outlet Surge Protector Tower, 3x USB Ports (3.1A Shared), 6 ft. Cord, 5-15P Plug, 1200 Joules, White

MODEL NUMBER: TLP66USB



Slim surge protection tower with USB charging safeguards your electronics against dangerous surges, spikes and line noise.

Features

Slim 5-Outlet Surge Protection Tower Safeguards Your Sensitive Electronics

Ideal for your home or office workstation, this Protect It!® five-outlet tower features a surge suppression rating of 1200 joules to defend your sensitive electronic components against even the strongest power surges and spikes. Because residential power outlets have three wires—hot line (H), neutral (N) and ground (G)—the TLP66USB protects all three, covering the two protection modes: full normal mode (H-N) and common mode (N-G/H-G).

5 NEMA 5-15R Outlets Accept a Wide Range of Electronic Devices

Plug your laptop, external hard drive, desk lamp or other home/office devices into the NEMA 5-15R outlets to protect them against dangerous surges, spikes and line noise. The outlets are split between two sides of the tower to give everyone equal access to them. They are also spread apart to allow easy connection of bulky transformers without blocking adjacent outlets.

3 USB Ports Share 3.1 Amps of Charging Power

USB-A ports are available for charging your smartphone, tablet and other USB mobile devices. They share 3.1A for charging multiple devices at the same time.

Premium Protection from EMI/RFI Line Noise Helps Your Equipment Perform Better

Various electromagnetic and radio sources found in virtually every home and business can cause disruptive interference on the AC line. Known as EMI (electromagnetic interference) and RFI (radio frequency interference), this line noise is a common cause of performance problems. This surge protector filters out disruptive line noise that can disturb your electronics and inflict hardware damage or data loss. This EMI/RFI filtering also helps your connected components perform better and last longer.

Includes the Latest Safety Features to Maintain Your Equipment's Well-Being

An on/off switch allows you easy one-touch control over all connected equipment. Red and green LEDs confirm at a glance that your plugged-in devices are grounded and protected.

Slim Tower Design Gives You Plenty of Options for Installation and Use

The TLP66USB fits easily into your home or office workspace, conference table or classroom, providing power and USB charging at your fingertips. Its slim design also makes the surge protector tower ideal for travel, fitting into your backpack, laptop bag or suitcase for use in hotels, dorms and cruise ships. The

Highlights

- Ideal for conference tables, home offices and other areas with multiple mobile devices
- 5 NEMA 5-15R outlets spaced widely apart to accommodate bulky transformers
- 1200 joules protect your valuable electronics against dangerous surges and spikes
- 3 USB ports share 3.1A for fast charging of phones, tablets and other mobile devices
- Right-angle NEMA 5-15P plug with braided 6 ft. cord allows connection in tight spaces

Applications

- Ensure critical devices, such as laptops and tablets, stay fully powered and charged during important conferences and meetings
- Filter potentially damaging line noise to improve connected equipment's performance and lifespan
- Safeguard valuable data against damage stemming from unexpected surges
- Charge a smartphone and tablet without taking up available AC outlets

Package Includes

- TLP66USB 5-Outlet Surge Protector Tower, White
- Owner's manual



Powering Business Worldwide



braided six-foot power cord and space-saving right-angle NEMA 5-15P plug allows connection in tight spaces, such as behind furniture.

Specifications

OVERVIEW	
UPC Code	037332260321
Product Type	Surge Protector
Charging Form Factor	Tower
Device Compatibility	Amazon Kindle; Laptop; Phone; Tablet
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Input Cord Gauge (AWG)	14
Maximum Surge Amps	1200
Input Plug Type	NEMA 5-15P
Input Cord Details	SJT-B
Input Cord Length (ft.)	6
Right-Angle Plug	No
Input Cord Length (m)	1.83
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	60 Hz
Output Receptacles	(5) 5-15R
Circuit Breaker (amps)	15
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
CHARGING	
Number of Charging Ports	4
Total Charging Watts	15.5
Charging Method	USB
Charging Port Type	USB A (FEMALE)
Charging Ports / Amps	(3) 3.1A
Overcharge Protection	No

SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	1200
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
UL1449 Let Through Rating	700,700,700
EMI / RFI Filtering	Yes
Immunity	Conforms to IEE 587/ANSI C62.41
Automatic Shut-Off	No
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
PHYSICAL	
Material of Construction	Plastic
Power Cord Color	Gray and White Braided Cord
Mounting Holes or Slots	Yes
Receptacle Color	Black
Unit Dimensions (hwd / in.)	2.000 x 7.080 x 7.080
Unit Dimensions (hwd / cm)	5.08 x 18 x 18
Unit Weight (lbs.)	1.8
Unit Weight (kg)	0.82
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	No
GaN Technology	No
STANDARDS & COMPLIANCE	
Product Certifications	CAN/CSA-C22.2 No. 269.3 (Canada); CAN/CSA-C22.2 No. 308 (Canada); NOM (Mexico); UL 1449; UL 497A; UL 1363
Product Compliance	FCC Part 68; RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$7,500 Ultimate Lifetime Insurance </td>



Powering Business Worldwide



1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.