

## Safe-IT 6-Outlet Surge Protector, Retractable USB Charger, 5-15R Outlets, 4 USB Charging Ports, 8 ft. (2.4 m) Cord, Antimicrobial Protection

MODEL NUMBER: TLP68UBAM



Safely charges and powers up to 10 devices, including laptops and tablets, during important work-from-anywhere meetings and conferences.

### Features

#### 6-Outlet Surge Protector Safeguards Your Sensitive Electronics

Ideal for your home or office workstation or travel use, this Safe-IT™ surge protector features a surge protection rating of 1080 joules to defend your sensitive electronic components against even the strongest power surges and spikes. Because residential power outlets have three wires—hot line (H), neutral (N) and ground (G)—the TLP68UBAM protects all three, covering the two protection modes: full normal mode (H-N) and common mode (N-G/H-G).

#### NEMA 5-15R Outlets Accept a Wide Range of Electronic Devices

Plug your computer, printer, wireless router, desk lamp or other home/office electronics into six NEMA 5-15R outlets to protect them against dangerous surges, spikes and line noise. Two outlets are spaced apart to accept bulky transformers or large plugs without blocking adjacent outlets.

#### Retractable USB Charger Offers Easy Access to Mobile Devices

The USB charger with retractable 4.5-foot (1.4-meter) cord clamps to the edge of your desk or work surface for convenient access to four USB-A ports, while the AC outlets remain out of your way. The USB ports share 3.4A for charging your smartphone, tablet and other USB mobile devices.

#### Filtering EMI/RFI Line Noise Helps Your Equipment Perform Better

This surge protector filters out disruptive electromagnetic and radio frequency interference that can inflict hardware damage or data loss. This EMI/RFI filtering also helps your connected components perform better and last longer.

#### Antimicrobial Protection Helps Provide a Safer, Cleaner and Healthier Work Environment

The Safe-IT TLP68UBAM features antimicrobial protection that helps resist the growth of bacteria, viruses, fungi, mold and mildew.

#### Premium Safety Features Protect Your Valuable Equipment

The on/off switch provides one-touch control over connected equipment. Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required. A green LED confirms your connected equipment is protected.

### Highlights

- 6 NEMA 5-15R outlets distribute AC power to connected home/office equipment
- 1080 joules protect your valuable electronics against dangerous surges and spikes
- 4 USB ports share 3.4A for fast charging of phones, tablets and other mobile devices
- Retractable USB charger clamps to your desk to keep mobile devices within easy reach
- Antimicrobial protection helps resist the growth of bacteria, viruses, fungi, mold and mildew

### Package Includes

- TLP68UBAM 6-Outlet Surge Protector with Retractable USB Charger
- Owner's manual

## Specifications

| OVERVIEW                           |  |
|------------------------------------|--|
| UPC Code                           | 037332265814   |
| Product Type                       | Surge Protector  |
| Charging Form Factor               | Strip  |
| Device Compatibility               | Phone; Tablet; Amazon Kindle   |
| INPUT                              |  |
| Nominal Input Voltage(s) Supported | 120V AC  |
| Recommended Electrical Service     | 120V (110-125V)  |
| Input Plug Features                | Right Angle (36D)  |
| Input Cord Gauge Type              | 14 gauge; SJT  |
| Voltage Compatibility (VAC)        | 120  |
| Maximum Surge Amps                 | 36000  |
| Input Plug Type                    | NEMA 5-15P   |
| Input Cord Length (ft.)            | 8  |
| Right-Angle Plug                   | No   |
| Input Cord Length (m)              | 2.44   |
| Integrated Cord Clip               | No   |
| OUTPUT                             |  |
| Frequency Compatibility            | 60 Hz  |
| Output (Watts)                     | 1800   |
| Output Receptacles                 | (6) 5-15R  |
| Circuit Breaker (amps)             | 15   |
| Transformer Accommodation          | (4) Yes  |
| Right-Angle Outlets                | Yes  |
| USER INTERFACE, ALERTS & CONTROLS  |  |
| Diagnostic LED(s)                  | Yes  |
| Switches                           | Combination AC circuit breaker and 2 position on/off power switch    |
| Diagnostic LED Details             | Built-in LED confirms suppressor "protection present" (green) status |
| CHARGING                           |  |
| Number of Charging Ports           | 4  |
| Total Charging Amps                | 3.4A   |



Powering Business Worldwide



|                                      |  |
|--------------------------------------|--|
| Total Charging Watts                 | 17   |
| Charging Method                      | USB  |
| Charging Port Type                   | (4) USB A (FEMALE)   |
| Charging Ports / Amps                | (4) 3.4A   |
| Overcharge Protection                | No   |
| <b>SURGE / NOISE SUPPRESSION</b>     |  |
| AC Suppression Joule Rating          | 1080   |
| AC Suppression Response Time         | < 1 ns   |
| Protection Modes                     | Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression |
| UL1449 Let Through Rating            | 400V   |
| EMI / RFI Filtering                  | Yes  |
| Automatic Shut-Off                   | Yes  |
| <b>DATALINE SURGE SUPPRESSION</b>    |  |
| Cable (Coax) Protection              | No   |
| Network (Ethernet) Protection        | No   |
| Telephone/DSL Protection             | No   |
| <b>PHYSICAL</b>                      |  |
| Material of Construction             | Plastic  |
| Power Cord Color                     | Black  |
| Housing Color                        | Black  |
| Mounting Holes or Slots              | No   |
| Receptacle Color                     | Black  |
| Shipping Weight (lbs.)               | 1.63   |
| Shipping Weight (kg)                 | 0.74   |
| Unit Dimensions (hwd / in.)          | 8.300 x 3.600 x 1.400  |
| Unit Dimensions (hwd / cm)           | 24 x 17 x 4.6  |
| Unit Weight (lbs.)                   | 1.8  |
| Unit Weight (kg)                     | 0.82   |
| <b>FEATURES &amp; SPECIFICATIONS</b> |  |
| Rotatable Outlets                    | No   |
| Antimicrobial                        | Yes  |
| GaN Technology                       | No   |
| <b>STANDARDS &amp; COMPLIANCE</b>    |  |



Powering Business Worldwide



|  |   |
|--|---|
| Product Certifications                                     | cUL Listed; UL 1449; UL 1363; UL Listed   |
| Product Compliance   | RoHS  |
| <b>WARRANTY &amp; SUPPORT</b>                              |   |
| Product Warranty Period (Worldwide)                        | Lifetime limited warranty   |
| Connected Equipment Insurance (U.S., Canada & Puerto Rico) | \$50,000 <a class="insuranceLink" href="//tripplite.eaton.com/support/insurance-policy">Ultimate Lifetime Insurance</a> |

1000 Eaton Boulevard  
 Cleveland, OH 44122  
 United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
 Eaton is a registered trademark. All other trademarks  
 are the property of their respective owners.