

## Protect It! 7-Outlet Surge Protector, 7-ft. Cord, 1080 Joules, Tel/Modem Protection, Silver Housing

MODEL NUMBER: TLP707TEL



### Highlights

- 7 outlets / 7-ft. cord
- 1080 joule rating
- 1 in/1 out tel/modem surge protection

### Package Includes

- TLP707TEL surge suppressor
- 6-ft. RJ11 cable
- Instruction manual and warranty information

### Description

Tripp Lite's TLP707TEL surge suppressor offers complete AC and phone line surge suppression for comprehensive protection of workstations, desktop PCs, telecom systems and other sensitive electronics. Heavy grade AC surge suppression shields connected equipment from damage and performance problems due to transient surges. Set of RJ11 telephone line suppression jacks protect dialup and DSL modem lines, fax machines, cordless phones and more. TLP707TEL offers 7 total outlets, 7 foot cord with space-saving angled plug, automatic cord management and diagnostic LEDs to warn of wiring problems and suppressor damage. Heavy grade AC suppression rated at 1080 joules shields equipment from surges and line noise. Attractive metallic silver housing with 3 designated transformer plug outlets offers convenient protection of desktop computer equipment and accessories. \$50,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only).

PLUG/OUTLETS: Input: NEMA5-15P/Output: 7 NEMA5-15R/7-ft. AC line cord

ELECTRICAL: 120V AC, 50/60Hz, 15A (Requires NEMA5-15R wall receptacle)

FORMAT: Unique on-end suppressor format supports the connection of up to 3 large transformer plugs on one side and 4 additional straight input plugs on the other

SUPPRESSION: AC: 150V RMS Clamping/1080 joules/400V UL1449 3rd Edition

### Features

- Offers complete AC and phone line surge suppression for comprehensive protection of workstations, desktop PCs, telecom systems and other sensitive electronics
- Heavy grade AC surge suppression shields connected equipment from damage and performance problems due to transient surges
- Set of RJ11 telephone line suppression jacks protect dialup and DSL modem lines, fax machines, cordless phones and more



- 7 total outlets
- 7 foot cord with space-saving angled plug, automatic cord management
- Diagnostic LEDs to warn of wiring problems and suppressor damage
- Heavy grade AC suppression rated at 1080 joules shields equipment from surges and line noise
- Attractive metallic silver housing
- 3 designated transformer plug outlets offer convenient protection of desktop computer equipment and accessories
- \$50,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)
- Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required

## Specifications

OVERVIEW	
UPC Code	037332119056
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Maximum Surge Amps	72000
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	7
Right-Angle Plug	Yes
Input Cord Length (m)	2.13
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(7) 5-15R
Circuit Breaker (amps)	15
Overload Protection	15A resettable combo switch / circuit breaker
Transformer Accommodation	(5) Yes
Outlet Orientation	Two rows of outlets, 3 widely spaced on one side for transformers, 4 closely spaced outlets on the other



Right-Angle Outlets	No
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Diagnostic LED(s)	Yes
Switches	Combination AC circuit breaker and 2 position on/off power switch
Diagnostic LED Details	Built-in LEDs confirm suppressor "protection present" (green) and "grounded" (red) status
<b>SURGE / NOISE SUPPRESSION</b>	
AC Suppression Joule Rating	1080
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping Voltage (RMS)	150
UL1449 Let Through Rating	400V
EMI / RFI Filtering	Up to 20 dB
Automatic Shut-Off	Yes
<b>DATALINE SURGE SUPPRESSION</b>	
Telephone/DSL Protection	Yes
Telephone/DSL Protection Details	1 line
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
<b>PHYSICAL</b>	
Antimicrobial Coating	No
Color	Silver
Color (AC Line Cord)	Black
Form Factors Supported	Supports floor / desktop placement
Housing Color	Metallic Silver
Integrated Keyhole Mounting Slots	Yes
Material of Construction	Plastic
Outlets Measurement (Center to Center)	Transformer Side Spacing = 61.8mm; Standard Outlet Side Spacing = 25.4mm
Receptacle Color	Black
Shipping Dimensions (hwd / cm)	31.75 x 12.19 x 5.33
Shipping Dimensions (hwd / in.)	12.50 x 4.80 x 2.10
Shipping Weight (kg)	0.68
Shipping Weight (lbs.)	1.50



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Unit Dimensions (hwd / cm)	5.00 x 4.09 x 27.71
Unit Dimensions (hwd / in.)	1.97 x 1.61 x 10.91
Unit Weight (kg)	0.57
Unit Weight (lbs.)	1.25
<b>SPECIAL FEATURES</b>	
Rotatable Outlets	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Canada	cUL
Approvals	Exceeds IEEE 587 category A&B specifications
UL1449 3rd Edition (AC Suppression)	UL1449 3RD EDITION
UL1363 (Power Tap)	UL1363
UL497A (Communications)	UL497A
FCC Part 68 (Communications)	FCC Part 68
Industry Canada (Communications)	Industry Canada
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$50,000 & <a href="http://www.tripplite.com/support/insurance-policy">Ultimate Lifetime Insurance</a>

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>