

Protect It! 7-Outlet Surge Protector 4-ft. Cord, 1080 Joules, 1 Diagnostic LED, Light Gray Housing

MODEL NUMBER: TLP74R



Highlights

- 7 outlets (6 right-angle outlets and 1 designated transformer outlet)
- 4-ft. cord
- 1080 joule rating

Package Includes

- TLP74R Surge Suppressor

Description

Tripp Lite's TLP74R offers economical AC surge suppression for protection of workstations, desktop PCs, telecom systems and other sensitive electronics. Built-in AC surge suppression shields connected equipment from damage and performance problems due to transient surges. TLP74R offers 7 total outlets (6 at right angle and 1 designated transformer plug outlet), 4 foot cord and diagnostic LED to warn of suppressor damage. AC suppression rated at 1080 joules shields equipment from surges and line noise. Attractive gray housing with keyhole mounting tabs offering convenient protection of desktop computer equipment and accessories. \$25,000 Ultimate Lifetime Insurance (USA & Canada Only).

PLUG/OUTLETS: Input: NEMA5-15P/Output: 7 NEMA5-15R/4-ft. AC line cord

ELECTRICAL: 120V AC, 60Hz, 15A (Requires NEMA5-15R wall receptacle)

FORMAT: Corded multi-outlet strip

SUPPRESSION: AC: 150V RMS Clamping/1080 joules/400V UL1449 Let-through

Features

- 1080 joules AC surge suppression shields equipment from the strongest surges and line noise
- 7 total AC outlets (6 right angle and 1 transformer plug outlet)
- 4 foot AC line cable
- Lighted on/off switch with integrated circuit breaker for overload protection of all outlets
- Diagnostic LED confirms surge suppression status
- Integrated keyhole slots provide convenient wall/desk mounting
- UL1449 3rd Edition Rated (400V all modes), UL1363 (Power Tap), cUL (Canada)
- Exceeds IEEE 587 category A & B surge suppression specifications
- \$25,000 Ultimate Lifetime Insurance (USA and Canada Only)
- Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing



equipment damage and indicating replacement is required

Specifications

OVERVIEW	
UPC Code	037332155658
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Maximum Surge Amps	36000
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	4
Right-Angle Plug	No
Input Cord Length (m)	1.22
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	60 Hz
Output (Watts)	1800
Output Receptacles	(7) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(4) Yes
Outlet Orientation	Single row
Right-Angle Outlets	Yes
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Switches	Combination AC circuit breaker and 2 position on/off power switch
Diagnostic LED Details	Built-in LED confirms suppressor "protection present" (green) status
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	1080
AC Suppression Response Time	< 1 ns



Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping Voltage (RMS)	150
UL1449 Let Through Rating	400V
Automatic Shut-Off	Yes
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
PHYSICAL	
Antimicrobial Coating	No
Color	Light Gray
Color (AC Line Cord)	Light Gray
Housing Color	Light Gray
Integrated Keyhole Mounting Slots	Yes
Keyhole Slot Mounting Measurement (Center to Center)	207mm
Material of Construction	Plastic
Outlets Measurement (Center to Center)	28.5mm
Receptacle Color	Light gray
Shipping Dimensions (hwd / cm)	5.08 x 10.92 x 35.56
Shipping Dimensions (hwd / in.)	2.00 x 4.30 x 14.00
Shipping Weight (kg)	0.50
Shipping Weight (lbs.)	1.10
Unit Dimensions (hwd / cm)	3.38 x 5.18 x 31.50
Unit Dimensions (hwd / in.)	1.33 x 2.04 x 12.4
Unit Weight (kg)	0.47
Unit Weight (lbs.)	1.04
SPECIAL FEATURES	
Rotatable Outlets	No
STANDARDS & COMPLIANCE	
Canada	cUL
Approvals	Exceeds IEEE 587 category A&B specifications



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

UL1449 3rd Edition (AC Suppression)	UL1449 3rd Edition
UL1363 (Power Tap)	UL1363
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$25,000 Ultimate Lifetime Insurance

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>