



## Eco-Surge 7-Outlet Surge Protector, 6 ft. (1.83 m) Cord, 1080 Joules, Individually-Controlled

### MODEL NUMBER: TLP76MSG



#### **Highlights**

- Individual outlet control
- 1080 joules
- 7 outlet / 6-ft cord
- Diagnostic LEDs

#### **Package Includes**

- TLP76MSG ECO-SURGE Home/Business Theater Surge Suppressor
- Instruction manual with warranty information

#### Description

The TLP76MSG offers reliable green surge technology that protects your computer and peripherals, as well as the environment and your wallet. Energy-saving outlet configuration reduces energy waste (phantom loads) by cutting AC power to unused peripherals. The TLP76MSG has one always-on outlet for those peripherals that need constant power like a fax machine, DVR or router. It also offer convenient individual outlet switches that allow users to select which device is turned on and off. The TLP76MSG has seven total outlets, a six-foot (1.8-meter) power cord and diagnostic LEDs to warn of wiring problems and suppressor damage. Network-grade AC suppression rated at 1080 joules shields equipment from surges and line noise. Designed with an attractive cool gray suppressor housing, the TLP76MSG can accommodate up to four transformer plug outlets offering convenient protection of desktop computer equipment and accessories.

#### **Features**

- Energy-saving green outlets allow individual outlet control using illuminated power switches for cutting power to peripherals not in use.
- Six green outlets have their own illuminated ON/OFF switch for cutting power to peripherals when they
  are not in use. One "Always On" outlet provides continuous power for devices such as DVRs (TiVo),
  cable and satellite boxes, modems, routers and fax machines.
- In addition to the individual illuminated outlet switches, an illuminated Master Switch controls power to all outlets (except the Always On outlet) at once. It can override other "ON" settings to cut power to all switched outlets at once.
- Protected (Green) LED assures protection is present & Always On (Red) LED indicates that the Always On outlet is receiving power.
- 1080 joules surge suppression rating with EMI/RFI line noise filtering help components perform at their peak (sharper, crisper video; deeper, fuller audio and longer component life spans).
- Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing
  equipment damage and indicating replacement is required

# **Specifications**

#### OVERVIEW

UPC Code

037332166074





INPUT		
Nominal Input Voltage(s) Supported	120V AC	
Recommended Electrical Service	120V (110-125V)	
Input Cord Gauge Type	14 gauge; SJT	
Input Cord Gauge (AWG)	14	
Voltage Compatibility (VAC)	120	
Maximum Surge Amps	72000	
Input Plug Type	NEMA 5-15P	
Input Cord Details	SJT	
Input Cord Length (ft.)	6	
Right-Angle Plug	No	
Input Cord Length (m)	1.83	
Integrated Cord Clip	No	
OUTPUT		
Output Capacity (VA)	120	
Output Capacity (Watts)	1800	
Frequency Compatibility	60 Hz	
Output Receptacles	(7) 5-15R	
Transformer Accommodation	(4) Yes	
Right-Angle Outlets	Yes	
Individually Controllable Load Banks	Yes	
USER INTERFACE, ALERTS & CON	TROLS	
Diagnostic LED(s)	Yes	
Switches	1 x Lighted Master Switch & 6 x Lighted Receptacle Switches	
LED Indicators	Protected (Green)" & Always On Receptacle (Red)	
SURGE / NOISE SUPPRESSION		
AC Suppression Joule Rating	1080	
AC Suppression Response Time	< 1 ns	
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression	
UL1449 Let Through Rating	400v	
EMI / RFI Filtering	Up to 40 dB	
Automatic Shut-Off	Yes	
DATALINE SURGE SUPPRESSION		





Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
PHYSICAL	
Material of Construction	Plastic
Power Cord Color	Gray
Housing Color	Gray
Mounting Holes or Slots	No
Slot or Hole Mount Measurement (Center to Center)	300 mm
Receptacle Color	Gray
Shipping Dimensions (hwd / in.)	2.00 x 4.20 x 17.00
Shipping Dimensions (hwd / cm)	5.08 x 10.67 x 43.18
Shipping Weight (lbs.)	1.80
Shipping Weight (kg)	0.82
Unit Dimensions (hwd / in.)	1.400 x 3.400 x 15.000
Unit Dimensions (hwd / cm)	3.56 x 8.64 x 38.1
Unit Weight (lbs.)	1.54
Unit Weight (kg)	0.70
Input Cord Color	Gray
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	No
STANDARDS & COMPLIANCE	
Product Certifications	CAN/CSA-C22.2 No. 269.3 (Canada); CAN/CSA-C22.2 No. 308 (Canada); cUL Listed; NOM (Mexico); UL 1449; UL 1363; UL Listed
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$25,000 <a class="insuranceLink" href="//tripplite.eaton.com/support/insurance-policy">Ultimate Lifetime Insurance</a>





1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.