

8-Outlet Surge Protector with DSL/Phone Line/Modem Surge Protection - 3150 Joules, 6 ft. (1.83 m) Cord

MODEL NUMBER: TLP806TELTAA



Protect your home and office electronics, including phones and modems, against surges, spikes and line noise.

Features

3150-Joule Surge Protection for Home or Office Electronics The 3150-joule rating means your computer, printer, scanner, external hard drive and other sensitive electronic components are protected against even the strongest surges and spikes. Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required. Built-in RJ11 jacks (1 in/2 out) prevent surges from damaging your modem/fax/phone equipment.

This TAA-compliant surge protector features full normal mode (H-N) and common mode (N-G/H-G) line surge suppression. It filters out disruptive EMI/RFI line noise that can cause equipment damage or data loss and exceeds IEEE 587 Category A and B surge suppression specifications.

Accepts Wide Range of Electronic Devices This 6-ft. (1.83 m) surge protector has eight NEMA 5-15R AC outlets, including three widely spaced outlets to accommodate bulky transformers without blocking other outlets. Built-in child-safety covers prevent accidental contact with unused outlets.

Premium Safety Features Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required. A lighted on/off switch provides one-touch control over connected equipment. An integrated 15A circuit breaker protects outlets against overloads. LEDs show grounding and protection status at a glance.

Fits Effortlessly Into Your Workstation This cable modem surge protector includes a 6-ft. (1.83 m) AC power cord long enough to reach distant outlets. A right-angle NEMA 5-15P plug allows furniture and equipment to move flush against the wall. Keyhole slots on bottom panel provide convenient wall or desk mounting options.

Compliant with TAA The TLP806TELTAA surge protector is compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

Lifetime Limited Warranty and Ultimate Lifetime Insurance This cable modem surge protector comes with a lifetime limited warranty and is backed by \$150,000 Ultimate Lifetime Insurance for any connected components damaged by a power surge (U.S., Canada and Puerto Rico only).

Highlights

- 8 5-15R NEMA outlets, including 3 for bulky transformers
- Surge suppression rating of 3150 joules
- Filters out threatening EMI/RFI line noise
- 15A resettable circuit breaker foils dangerous overloads
- 6-ft. (1.83 m) power cord with right-angle 5-15P plug for connecting in tight spaces

Applications

- Safeguards your computer, printer and fax from dangerous surges
- Protects your phones, wireless routers and broadband modems, as well as desk lamps and small appliances
- Shields TVs, DVD players, video game consoles, streaming media players, sound systems and device chargers from energy spikes

Package Includes

- Safeguards your computer, printer and fax from dangerous surges
- Protects your phones, wireless routers and broadband modems, as well as desk lamps and small appliances
- Shields TVs, DVD players, video game consoles, streaming media players, sound systems and device chargers from energy spikes

Specifications

OVERVIEW	
UPC Code	037332224903
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Cord Gauge Type	14 gauge; SJT
Input Cord Gauge (AWG)	14
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Details	SJT
Input Cord Length (ft.)	6
Right-Angle Plug	Yes
Input Cord Length (m)	1.83
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	60 Hz
Output Receptacles	(8) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(6) Yes
Outlet Orientation	Single row of 5, plus a second row of 3 for transformer accommodation
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Switches	Combination AC circuit breaker and 2-position red illuminated on/off power switch
Diagnostic LED Details	Built-in LEDs confirm suppressor "protection present" (green) and "grounded" (red) status
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	3150
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
UL1449 Let Through Rating	400 L-N, 500 L-G, 500 N-G
EMI / RFI Filtering	Up to 40 dB



Powering Business Worldwide



Automatic Shut-Off	No
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection Details	1 line
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	Yes
PHYSICAL	
Material of Construction	Plastic
Power Cord Color	Light Gray
Housing Color	Light Gray
Mounting Holes or Slots	Yes
Receptacle Color	Light gray
Shipping Dimensions (hwd / in.)	2.00 x 7.40 x 11.50
Shipping Weight (kg)	0.86
Unit Dimensions (hwd / in.)	10.500 x 3.900 x 2.200
Unit Dimensions (hwd / cm)	9.8 x 5.6 x 26.6
Unit Weight (lbs.)	1.52
Unit Weight (kg)	0.69
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	No
STANDARDS & COMPLIANCE	
Product Certifications	CAN/CSA-C22.2 No. 269.3 (Canada); CAN/CSA-C22.2 No. 308 (Canada); cUL Listed; NOM (Mexico); UL 1449; UL 497A; UL 1363; UL Listed
Product Compliance	FCC Part 68; RoHS; Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$150,000 Ultimate Lifetime Insurance

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.