

# Protect It! 230V Surge Protector with 8 Schuko Type F Outlets, German Plug, 2280 Joules

MODEL NUMBER: TLP82D



### Highlights

- 8 safety outlets
- 2 m power cord with German plug
- 2280 joule rating

### Package Includes

- TLP82D surge suppressor
- Instruction manual and warranty information

### Description

Tripp Lite's Protect It!™ TLP82D offers economical AC surge suppression for full protection of 220-250V home computers, printers, scanners, and desk lamps. The TLP825D offers 8 Schuko Type F outlets and a 2 meter AC line cord. Internal safety covers protect against accidental contact with unused outlets.

### Features

- Protect It!™ TLP82D offers economical AC surge suppression
- 2280 joules AC surge suppression shields equipment from surges and line noise
- 8 Schuko outlets protect computers and peripherals
- 2 m Cord with German plug
- Protected/Grounded LED's
- Internal safety covers protect against accidental contact with unused outlets

## Specifications

OVERVIEW	
UPC Code	037332145437
INPUT	
Nominal Input Voltage(s) Supported	230V AC
Recommended Electrical Service	230V (220-250V)
Voltage Compatibility (VAC)	220-250
Input Plug Type	German
Input Cord Length (ft.)	6
Right-Angle Plug	Yes



Powering Business Worldwide



Input Cord Length (m)	1.83
Integrated Cord Clip	No
<b>OUTPUT</b>	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(8) Schuko Type F
Circuit Breaker (amps)	10
Transformer Accommodation	(5) Yes
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Diagnostic LED(s)	Yes
Diagnostic LED Details	Grounded/Protected
<b>SURGE / NOISE SUPPRESSION</b>	
AC Suppression Joule Rating	2280
Automatic Shut-Off	No
<b>DATALINE SURGE SUPPRESSION</b>	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
<b>PHYSICAL</b>	
Color	Black
Power Cord Color	Black
Housing Color	Black
Mounting Holes or Slots	No
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	15.80 x 2.25 x 7.60
Shipping Dimensions (hwd / cm)	40.13 x 5.72 x 19.30
Shipping Weight (lbs.)	2.10
Shipping Weight (kg)	0.95
Unit Dimensions (hwd / in.)	12.070 x 4.610 x 1.930
Unit Dimensions (hwd / cm)	30.66 x 11.71 x 4.90
Unit Weight (lbs.)	1.50
Unit Weight (kg)	0.68
<b>FEATURES &amp; SPECIFICATIONS</b>	



Powering Business Worldwide



Rotatable Outlets	No
Antimicrobial	No
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.