

Protect It! 6-Outlet Surge Protector, 6 ft. (1.83 m) Cord, 3040 Joules, Tel/DSL Protection

MODEL NUMBER: TR-6FM



Highlights

- 6 outlets/6-ft. (1.83 m) cord
- 3040 joule rating
- Modem/fax surge protection

Package Includes

- TR-6FM Surge Suppressor
- 6-ft. (1.83 m) Telephone cord
- Child Safety Covers
- Color-coded cord identifiers
- Warranty information with instruction manual

Description

The TR-6FM Surge Suppressor has six outlets and a six-foot (1.8 meters) cord with a space-saving right-angle plug. The unit has 3040 joules of surge energy absorption to handle the strongest surges. Built-in RJ11 jacks prevent surges from damaging your modem/fax/phone equipment. A six-foot telephone cord is also included. Diagnostic LEDs alert the user to potential power problems. The Super Surge Alert+Tel comes with child safety covers and color-coded cord identifiers.

Features

- 6 outlets with child safety covers
- 6-ft. (1.83 m) cord with space-saving right-angle plug
- Built-in RJ11 jacks prevent surges from damaging your modem/fax/phone equipment; 6-ft. (1.83 m) telephone cord included
- Surge energy absorption: 3040 joules; 85,000 amps
- 15 amp circuit breaker
- 3 diagnostic LEDs indicate AC present, line fault & protection present
- EMI/RFI noise filtering
- Logical outlet spacing accommodates transformers without blocking remaining outlets
- Keyhole supports for wall mounting
- Recessed and lighted power switch
- Color-coded cord identifiers
- \$50,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only) covers connected equipment
- Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required

Specifications

OVERVIEW	
UPC Code	037332010612



Powering Business Worldwide



INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Cord Gauge (AWG)	14
Voltage Compatibility (VAC)	120
Maximum Surge Amps	105000
Input Plug Type	NEMA 5-15P
Input Cord Details	SJT
Input Cord Length (ft.)	6
Right-Angle Plug	Yes
Input Cord Length (m)	1.83
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(6) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(2) Yes
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Switches	Two position red illuminated on/off power switch
Diagnostic LED Details	PROTECTION PRESENT (green), LINE FAULT (red) and LINE OK (green)
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	3040
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
AC Suppression Surge Current Rating	78,500 amps
UL1449 Let Through Rating	400V - UL Verified
EMI / RFI Filtering	Yes
Immunity	Conforms to IEE 587 / ANSI C62.41
Automatic Shut-Off	Yes
DATALINE SURGE SUPPRESSION	



Powering Business Worldwide



Telephone/DSL Protection Details	1 line
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	Yes
PHYSICAL	
Material of Construction	Plastic
Power Cord Color	Light Gray
Housing Color	Light Gray
Mounting Holes or Slots	Yes
Slot or Hole Mount Measurement (Center to Center)	88.8 mm
Outlets Measurement (Center to Center)	Distance between horizontal outlets = 44.20mm; Distance between vertical outlets = 39mm
Receptacle Color	Light gray
Shipping Dimensions (hwd / in.)	2.00 x 6.00 x 12.50
Shipping Dimensions (hwd / cm)	5.08 x 15.24 x 31.75
Shipping Weight (lbs.)	2.30
Shipping Weight (kg)	1.04
Unit Dimensions (hwd / in.)	1.750 x 3.500 x 9.500
Unit Dimensions (hwd / cm)	4.45 x 8.9 x 24.13
Unit Weight (lbs.)	1.65
Unit Weight (kg)	0.75
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	No
STANDARDS & COMPLIANCE	
Product Certifications	UL 1449; UL 497A
Product Compliance	FCC Part 68; RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$50,000 Ultimate Lifetime Insurance



Powering Business Worldwide



1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.