



Powering Business Worldwide

10-ft. USB A/B Cable (Adjustable Right Angle A Male to B Male Connector)

MODEL NUMBER: U012-010



Highlights

- Adjustable "A" connector allows for multiple exit configurations
- Premium double-shielded USB 2.0 cable with tinned copper braid and aluminum mylar foil feature twisted data lines
- Gold plated contacts provide superior conductivity for low and high speed devices

System Requirements

- USB port and device

Package Includes

- 10ft USB A/B Cable w/Adjustable Angle A Connector

Description

Tripp Lite's 10-ft. Adjustable "A" connector USB A/B device cable is designed to connect a USB device to the USB port on a computer or USB hub. Adjustable angle connector allows the cable to exit at any angle...perfect where space is limited. This high quality cable delivers the performance and reliability you expect from a USB cable. The cable features gold plated contacts for superior conductivity. It is manufactured with molded connectors which include integral strain relief to ensure durability. Double shielding provides maximum EMI/RFI protection. Tripp Lite warrants this product to be free from defects in materials and workmanship for life.

Features

- Two elbow joints allow for Up-Down-Left-Right exit configurations where space constraints are an issue
- Premium double-shielded USB 2.0 cable with tinned copper braid and aluminum Mylar foil feature twisted data lines
- Gold plated copper contacts provide superior conductivity
- Molded connectors which include integral strain relief to ensure durability
- Tripp Lite warrants this product to be free from defects in materials and workmanship for life

Specifications

OVERVIEW	
UPC Code	037332121998
CONNECTIONS	
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	USB B (MALE)
PHYSICAL	



Powering Business Worldwide

Color	Black
Cable Length (ft.)	10
Cable Length (m)	3.05
Shipping Dimensions (hwd / in.)	9.25 x 6.75 x 0.50
Shipping Dimensions (hwd / cm)	23.50 x 17.14 x 1.27
Shipping Weight (lbs.)	0.20
Shipping Weight (kg)	0.09
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.