

10-inch USB A/A Extension Cable (A Female to Adjustable Right Angle A Male Connector)

MODEL NUMBER: U014-10I



Description

Tripp Lite's 10-inch Adjustable, "A" Male connector USB A/A extension cable is designed to extend the length of an existing USB cable. This high quality cable delivers the performance and reliability you expect from a USB cable, as well as providing multiple exit direction options, via two hinged joints. The cable features gold plated contacts for superior conductivity. It is manufactured with molded connectors which include integral strain relief to ensure durability. Double shielding provides maximum EMI/RFI protection. Tripp Lite warrants this product to be free from defects in materials and workmanship for life.

Features

- Two elbow joints allow for Up-Down-Left-Right exit configurations where space constraints are an issue
- Premium double-shielded USB 2.0 cables with tinned copper braid and aluminum Mylar foil feature twisted data lines
- Gold plated copper contacts provide superior conductivity
- · Molded connectors which include integral strain relief to ensure durability
- Tripp Lite warrants this product to be free from defects in materials and workmanship for life

Specifications

OVERVIEW	
UPC Code	037332122018
Technology	USB 2.0 (High Speed)
CONNECTIONS	
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	USB A (FEMALE)
PHYSICAL	

Highlights

- Adjustable "A" Male connector allows for multiple exit configurations
- Premium double-shielded USB 2.0 cable with tinned copper braid and aluminum mylar foil feature twisted 28/20 AWG data lines
- Gold plated contacts provide superior conductivity for low and high speed devices

System Requirements

• USB port and device

Package Includes

 10inch USB A/A Cable w/Adjustable Angle A Male Connector



Color	Black	
Cable Length (ft.)	0.83	
Cable Length (m)	0.25	
Cable Length (in.)	10	
Shipping Dimensions (hwd / in.)	9.25 x 6.75 x 0.50	
Shipping Dimensions (hwd / cm)	23.50 x 17.14 x 1.27	
Shipping Weight (lbs.)	0.07	
Shipping Weight (kg)	0.03	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

1000 Eaton Boulevard

Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.