

## USB 2.0 A/B Coiled Cable (M/M), 10 ft. (3.05 m)

MODEL NUMBER: **U022-010-COIL**



Connects high-speed USB 2.0 peripherals with a USB-B port to your computer, laptop or other compatible USB-A device. Ideal for printers and scanners.

### Description

The U022-010-COIL USB 2.0 Hi-Speed A/B Coiled Cable (M/M) connects your computer, laptop or other compatible USB-A device to a USB-B peripheral, such as printers and scanners. This 10-ft. (3.05 m) cable supports data transfer rates up to 480 Mbps for both low- and high-speed devices, including multimedia applications.

The specially coiled cable takes up much less space than a regular 10-ft. (3.05 m) cable. It also resists tangles and knots, making it convenient to store in your car or carry in your purse, backpack or laptop bag. Molded nickel-plated connectors ensure excellent conductivity. Integral strain relief ensures the cable and connectors last a long time. A rugged PVC jacket protects twisted 28 AWG data lines and 24 AWG power lines.

### Features

#### Connect Your USB Type-B Peripherals to Your Computer

- Ideal for printers and scanners
- Supports data transfer rates up to 480 Mbps
- Backward compatible with earlier USB generations

#### Coiled to Take Up Less Space than Regular 10-ft. (3.05 m) Cable

- Resists tangles and knots
- Stores perfectly in car, purse, backpack or laptop bag

#### First-Rate Construction for Superior Signal Transfer

- Molded nickel-plated connectors for optimal signal quality
- Integral strain relief for long life
- Twisted 28/24 AWG data/power lines
- Flexible PVC jacket easy to install in tight spaces

## Specifications

### Highlights

- Supports data transfer rates up to 480 Mbps
- Molded nickel-plated connectors
- Twisted 28/24 AWG data/power lines
- 10-ft. (3.05 m) cable is coiled to take up less space

### System Requirements

- Device requiring USB cable
- USB 2.0 performance only when used with USB 2.0 device and USB 2.0 controller

### Package Includes

- U022-010-COIL USB 2.0 Hi-Speed A/B Coiled Cable (M/M), 10-ft. (3.05 m)



<b>OVERVIEW</b>	
UPC Code	037332197283
Technology	USB 2.0 (High Speed)
<b>PHYSICAL</b>	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	10
Cable Length (m)	3.05
Shipping Dimensions (hwd / cm)	1.27 x 17.78 x 24.13
Shipping Dimensions (hwd / in.)	0.50 x 7.00 x 9.50
Shipping Weight (kg)	0.06
Shipping Weight (lbs.)	0.14
<b>CONNECTIONS</b>	
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	USB B (MALE)
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	RoHS-Compliant
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>