

USB 2.0 A to B Cable with Ferrite Chokes (M/M), 3 ft. (0.91 m)

MODEL NUMBER: **U023-003**



Description

This gold USB 2.0 A/B device cable meets or exceeds USB 2.0 specifications. Connects a USB device to a USB port on a computer or hub. Molded ferrite chokes add additional shielding properties for noisy environments. Backward compatible with older USB 1.1 applications as well. USB 2.0 cabling includes superior foil shielding for reliable, error-free data communications. The significantly faster data transfer rates of USB 2.0 (up to 480 Mbps) make them perfect for multimedia applications. Features gold-plated connectors and gold-plated copper contacts for superior conductivity. The cable is manufactured with molded connectors and integral strain relief for extra durability and long life.

Features

- USB 2.0 certified
- Supports faster data transfer rate (1.5 to 480 Mbps) for low speed and high speed devices including multimedia applications
- Premium double-shielded cables with tinned copper braid and aluminum Mylar foil, Ferrite chokes
- Gold plated connectors and gold plated copper contacts for superior conductivity.
- Molded connectors and integral strain relief for extra durability and long life.

Specifications

OVERVIEW	
UPC Code	037332174253
Technology	USB 2.0 (High Speed)
Cable Type	Passive
CONNECTIONS	
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	USB B (MALE)

Highlights

- Meets or Exceeds USB 2.0 Specifications
- Supports faster data transfer rate (1.5 to 480 Mbps) for low speed and high speed devices, including multimedia applications
- Premium double-shielded cables with tinned copper braid and aluminum mylar foil and Ferrite chokes, feature twisted 28AWG data lines, and 24AWG power lines.
- Gold plated connectors provide superior conductivity

System Requirements

- Any USB device requiring a USB cable with extra shielding capabilities
- USB2.0 performance only when used with USB2.0 device and USB2.0 controller

Package Includes

- 3-ft. (0.91 m) USB 2.0 Gold Cable USB-A to USB-B with Ferrite Chokes



Powering Business Worldwide

TRIPP LITE
SERIES

Connector Style	Straight
PHYSICAL	
Cable Jacket Color	Black
Cable Length (ft.)	3
Cable Length (m)	0.91
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.15
Shipping Weight (kg)	0.07
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
ENVIRONMENTAL	
Operating Temperature Range	14° to 122°F (-10° to 50°C)
Storage Temperature Range	5° to 140°F (-15° to 60°C)
Operating Humidity Range	0% to 90% RH, Non-Condensing
Storage Humidity Range	0% to 78% RH, Non-Condensing
FEATURES & SPECIFICATIONS	
USB Specification	USB 2.0 (up to 480 Mbps)
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.