

USB 2.0 All-in-One Keystone/Panel Mount Extension Cable (M/F), Angled Connector, 1 ft. (0.31 m)

MODEL NUMBER: **U024-001-KPA-BK**



Adds a USB Type-A female port to a fixed location, such as a universal keystone wallplate, panel, podium or kiosk. Gives your conference room, classroom, home theater room or retail establishment a professional, clutter-free look.

Features

Mount a USB 2.0 Type-A Port in a Fixed Location

- Keystone design for easy snap-in installation in wallplate or panel
- Includes panel mount adapter for installation in podium or kiosk
- Angled female connector for easy installation in tight spaces
- Data transfer rates up to 480 Mbps
- Hides components out of sight to eliminate cable clutter
- Backward compatible with earlier USB generations

Premium Construction for Superior Signal Transfer

- Foil and braid shielding for error-free signal quality and EMI/RFI protection
- Molded nickel-plated connectors and gold-plated copper contacts
- Integral strain relief for long life
- Twisted 28/24 AWG data/power lines
- Rugged PVC jacket

Specifications

OVERVIEW	
UPC Code	037332195715
Product Type	USB Keystone
Technology	USB 2.0 (High Speed)

Highlights

- Connects two USB-A devices, such as computers and flash drives
- Data transfer rates up to 480 Mbps
- Premium double shielding for error-free signal quality
- Twisted 28/24 data/power lines
- Angled female connector for easy installation in tight spaces

Package Includes

- U024-001-KPA-BK USB 2.0 Hi-Speed All-in-One Keystone/Panel Mount Extension Cable (M/F), 1 ft.



Powering Business Worldwide

TRIPP LITE
SERIES

Cable Type	Passive
CONNECTIONS	
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	USB A (FEMALE)
Connector Style	Angled
PHYSICAL	
Cable Jacket Color	Black
Cable Length (ft.)	1
Cable Length (m)	0.30
Shipping Dimensions (hwd / in.)	9.00 x 0.50 x 7.00
Shipping Dimensions (hwd / cm)	22.86 x 1.27 x 17.78
Shipping Weight (lbs.)	0.30
Shipping Weight (kg)	0.14
ENVIRONMENTAL	
Operating Temperature Range	14° to 122°F (-10° to 50°C)
Storage Temperature Range	5° to 140°F (-15° to 60°C)
Operating Humidity Range	0% to 90% RH, Non-Condensing
Storage Humidity Range	0% to 80% RH, Non-Condensing
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.