


USB 2.0 Panel Mount Cable, 5-Pin Motherboard IDC to USB-A (F/F), 3 ft. (0.91 m)

MODEL NUMBER: **U024-003-5P-PM**



Connects your computer's motherboard to a panel-mounted USB-A port that can be installed in a computer, booth, kiosk or podium.

Description

The U024-003-5P-PM USB 2.0 Hi-Speed Panel Mount Cable connects to a computer's motherboard to add a panel-mounted USB Type-A port. In addition to the front panel of a computer, the USB-A port can be installed in a trade show booth, retail kiosk or teacher's or lecturer's podium, allowing you to conveniently connect a thumb drive or other USB device. The PCB header terminates on almost any five-pin motherboard.

The 3-ft. (0.91 m) cable supports data transfer rates up to 480 Mbps and is backward compatible with previous USB generations. Gold-plated contacts resist corrosion and ensure optimal signal transfer. Premium double-shielded cables with aluminum braid and aluminum Mylar foil feature twisted 28 AWG data lines and 24 AWG power lines. PVC jacket with molded connectors and integral strain relief provides durability and long life. Mounting screws included.

Features

Adds a Panel-Mounted USB-A Port Allows convenient USB access from a trade show booth, retail kiosk or lecturer's podium
5-pin PCB header terminates on computer's motherboard
Supports data transfer speeds up to 480 Mbps
Backward compatible with previous USB generations

Premium Construction for Premium Performance Corrosion-resistant gold-plated contacts for optimal signal transfer
 Fully molded construction with strain relief for durability and long life
 Flexible PVC jacket easy to install in tight spaces
 Double shielding with aluminum braid, aluminum Mylar foil and twisted 28/24 AWG data/power lines
 Mounting screws included

Specifications

OVERVIEW	
UPC Code	037332191113
Technology	USB 2.0 (High Speed)
Cable Type	Passive

Highlights

- Supports data transfer speeds up to 480 Mbps
- 5-pin PCB header connects to computer's motherboard
- USB-A port attaches with included screws
- Corrosion-resistant gold-plated contacts
- Backward compatible with previous USB generations

System Requirements

- Computer with 5-pin motherboard connector

Package Includes

- U024-003-5P-PM USB 2.0 Hi-Speed Panel Mount Cable, 3 ft.
- (2) Mounting screws



Powering Business Worldwide

TRIPP LITE
SERIES

CONNECTIONS	
Side A - Connector 1	5 PIN IDC (FEMALE)
Side B - Connector 1	USB A (FEMALE)
Connector Style	Straight
PHYSICAL	
Cable Jacket Color	Black
Cable Length (ft.)	3
Cable Length (m)	0.91
Shipping Dimensions (hwd / in.)	7.00 x 9.00 x 0.50
Shipping Dimensions (hwd / cm)	17.78 x 22.86 x 1.27
Shipping Weight (lbs.)	0.12
Shipping Weight (kg)	0.05
ENVIRONMENTAL	
Operating Temperature Range	14° to 122°F (-10° to 50°C)
Storage Temperature Range	5° to 140°F (-15° to 60°C)
Operating Humidity Range	0% to 90% RH, Non-Condensing
Storage Humidity Range	0% to 83% RH, Non-Condensing
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.