

2-Port USB 2.0 Desktop Extension Cable (M/2xF), 5 ft. (1.52 m)

MODEL NUMBER: **U024-005-DSK2**



Converts your computer's USB-A port to 2 USB-A ports and extends them up to 5 ft away. Ideal for connecting thumb drives, digital cameras and other USB-A devices.

Features

Expands an Existing USB-A Port to 2 Ports and Extends Them an Extra 5 ft.

- Move a hard-to-reach USB port within easy access
- Ideal for connecting external hard drives, thumb drives, digital cameras and other USB-A devices
- Features one USB 2.0 data/power port and one power-only port
- Supports data transfer rates up to 480 Mbps
- Backward compatible with earlier USB generations

First-Rate Construction for Superior Signal Transfer

- Premium foil and braid shielding for EMI/RFI noise protection
- Molded nickel-plated connectors for optimal signal quality
- Integral strain relief for long life
- Twisted 28/24 AWG data/power lines
- Flexible PVC jacket easy to install in tight spaces
- Black padded non-sliding base

Specifications

OVERVIEW	
UPC Code	037332199348
Technology	USB; USB 2.0 (High Speed)

Highlights

- Features one USB 2.0 data/power port and one power-only port
- Supports data transfer rates up to 480 Mbps
- Premium foil and braid shielding
- Backward compatible with earlier USB generations
- Twisted 28/24 AWG data/power lines

System Requirements

- Computer, laptop or other device with USB-A port

Package Includes

- U024-005-DSK2 2-Port USB 2.0 Hi-Speed Desktop Extension Cable (M/2xF), 5 ft.



INPUT	
Maximum Input Amps	2
CHARGING	
Total Charging Watts	10
PHYSICAL	
Color	Black
Material of Construction	PVC
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	4.5mm
Cable Length (ft.)	5
Cable Length (m)	1.52
Shipping Dimensions (hwd / cm)	13.49 x 10.01 x 1.27
Shipping Dimensions (hwd / in.)	5.31 x 3.94 x 0.50
Shipping Weight (kg)	0.09
Shipping Weight (lbs.)	0.20
Unit Packaging Type	Polybag
ENVIRONMENTAL	
Operating Temperature Range	32 to 104 F (0 to 40 C)
Storage Temperature Range	14 to 131 F (-10 to 55 C)
Relative Humidity	5% to 90% RH, Non-Condensing
Operating Humidity Range	0% to 90% RH, Non-Condensing
Storage Humidity Range	0% to 90% RH, Non-Condensing
Power Provided to Connected Device(s)	10W (5V/2A)
CONNECTIONS	
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	(2) USB A (FEMALE)
Connector Plating	Nickel
Contact Plating	Gold
FEATURES & SPECIFICATIONS	
Data Transfer Rate	480 Mbps



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

USB Specification	USB 2.0 (up to 480 Mbps)
STANDARDS & COMPLIANCE	
Certifications	Tested to RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>