

## USB 2.0 Active Extension Repeater Cable (A M/F), 10M (33 ft.)

MODEL NUMBER: **U026-10M**



### Description

Tripp Lite's 10-meter ( 33 ft. ) USB 2.0 active extension cable is a bus powered extension cable that can be used to increase the length of a device cable without the worry of signal loss and potential performance problems. USB limits a cable's length to 16ft. Any length above 16 feet requires the use of an active cable such as this one. This cable has a signal booster built in. The overall cable length can be extended up to 131ft by daisy chaining up to 4 of these active cables. The cable must be plugged directly into a USB port (either on the PC or a hub). Use a standard 6' 10' or 15' USB A-B cable to reach the desired distance. The U026-10M provides up to 150mA of power to the connected device. If your device requires more than 150mA of power, it will either need to have its own power supply; or, to be plugged into a powered USB 2.0 hub (such as U222-004-R) that is connected to the U026-10M.

### Features

- 10 meter ( 33 ft. ) USB2.0 Active Extension Cable, USB-A Male to USB-A Female
- Full 480Mbps Transfer rate, as well as backward compatible to USB 1.1 ( 12Mbps )
- Daisy Chain four cables for a total of 40 Meters ( 131ft )
- Bus Powered...no external power required
- Compatible with all major operating systems....Plug-and-Play; no software to load
- The U026-10M provides up to 150mA of power to the connected device. If your device requires more than 150mA of power, it will either need to have its own power supply; or, to be plugged into a powered USB 2.0 hub (such as U222-004-R) that is connected to the U026-10M.

## Specifications

### OVERVIEW

### Highlights

- Extends and Boosts the signal to any USB device
- Supports data transfer speeds up to 480Mbps
- Built in Repeater maintains Hi-Speed USB signal quality, and electrical / timing specifications
- Plug and Play....Compatible with all major operating systems

### System Requirements

- USB 2.0 enabled computer ( Windows or MAC )
- The U026-10M provides up to 150mA of power to the connected device. If your device requires more than 150mA of power, it will either need to have its own power supply; or, to be plugged into a powered USB 2.0 hub (such as U222-004-R) that is connected to the U026-10M.

### Package Includes

- 10-Meter ( 33 ft. ) USB2.0 A/A Hi-Speed Active Extension / Repeater Cable



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

UPC Code	037332173263
Technology	USB 2.0 (High Speed); USB
<b>INPUT</b>	
Cable Length (ft.)	32.8
Cable Length (m)	10
<b>PHYSICAL</b>	
Color	Black
Shipping Dimensions (hwd / cm)	5.08 x 12.70 x 15.24
Shipping Dimensions (hwd / in.)	2.00 x 5.00 x 6.00
Shipping Weight (kg)	0.34
Shipping Weight (lbs.)	0.76
<b>CONNECTIONS</b>	
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	USB A (FEMALE)
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	RoHS Compliant
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>