

USB-A to USB-C Cable, Right-Angle USB-C, USB 2.0, (M/M), 6 ft. (1.83 m)

MODEL NUMBER: U038-006-CRA



USB-A to C cable connects a smartphone or other USB-C device to the USB-A port on your computer, wall charger or car charger.

Features

USB Type-A to USB Type-C Cable Connects a USB-C Mobile Device to Your Computer This six-foot right-angle USB-C cable allows you to connect a device with a USB-C or Thunderbolt 3 port to a USB-enabled computer, charger, hard drive, hub or other peripheral for the purpose of charging, powering, syncing or transferring data. It is compatible with any device with a USB-C or Thunderbolt 3 port, including tablets, smartphones, MacBooks, Ultrabooks and Chromebooks.

Transfers Data and Charges Devices at USB 2.0 Speeds The USB-A to C cable supports USB 2.0 data transfer speeds up to 480 Mbps. The cable is backward compatible with previous USB generations, allowing you to use it with older equipment.

Reversible USB-C Connector Attaches in Either Direction Unlike traditional USB cables that connect in only one direction, the reversible USB-C male connector plugs into a USB-C or Thunderbolt 3 port in either direction for a fumble-free connection every time.

Right-Angle USB-C Plug Makes Connecting in Tight Spaces Easier The space-saving right-angle USB-C plug is easy to install in confined spaces, such as behind your computer desk or workstation. The right-angle construction also relieves strain on the cable and connector and prevents the cable from bending awkwardly.

Specifications

OVERVIEW	
UPC Code	037332214126
Technology	USB 2.0 (High Speed)
USB Cable Type	Passive

Highlights

- Right-angle USB-C plug permits easier connection in confined or hard-to-reach spaces
- Supports USB 2.0 speeds up to 480 Mbps to ensure efficient data transfers
- Reversible USB-C plug connects in either direction for immediate no-fuss use
- USB-A to USB-C cable compatible with all USB-A, USB-C and Thunderbolt 3 devices

Applications

- Charge and sync a USB-C mobile device from a USB-A wall charger up to 6 ft. away
- Connect a printer or scanner to a desktop computer's hard-to-reach rear USB-C port
- Transfer data between an external hard drive or flash drive and your computer or laptop

System Requirements

- Device with a USB-C or Thunderbolt 3 port
- Device with a USB-A port

Package Includes

- U038-003-CRA USB Type-A to Type-C Cable, M/M, 6 ft.



PHYSICAL	
Material of Construction	PVC
Cable Jacket Color	White
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	3.5 mm
Cable Length (ft.)	6
Cable Length (m)	1.83
Cable Length (in.)	72
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Weight (lbs.)	0.08
Shipping Weight (kg)	0.04
Unit Packaging Type	Polybag
ENVIRONMENTAL	
Operating Temperature Range	32 to 113 F (0 to 45 C)
Storage Temperature Range	-40 to 158 F (-40 to 70 C)
Operating Humidity Range	10% to 85% RH, Non-Condensing
Storage Humidity Range	5% to 90% RH, Non-Condensing
CONNECTIONS	
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	USB C (MALE) - RIGHT ANGLE
Connector Plating	Nickel
Contact Plating	Gold
FEATURES & SPECIFICATIONS	
USB Specification	USB 2.0 (up to 480 Mbps)
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

<https://www.tripplite.com/products/product-certification-agencies>