


Safe-IT USB-A to USB-C Antibacterial Cable, USB 2.0, Ultra Flexible (M/M), Light Blue, 6 ft. (1.8 m)

MODEL NUMBER: U038AB-006-S-LB



USB cable with antibacterial material connects a smartphone or other USB-C device to the USB-A port on your computer, wall charger or car charger.

Features

USB Cable Charges and Syncs Your Phone or Other USB-C Mobile Device

This USB sync/charge cable (M/M) connects your smartphone, tablet, MacBook Pro, Windows laptop or other USB-C device to the USB-A port on a computer, wall charger or car charger. It supports power output up to 20V/3A (60W), which is sufficient for fast charging and powering most mobile devices. It also simultaneously synchronizes and transfers data at USB 2.0 speeds up to 480 Mbps.

Innovative Soft Cable Jacket Prevents Tangles, Allows Flexible Bends

Very flexible for convenient on-the-go connections, this ultra-soft silicone-layered jacket avoids nasty tangles in your backpack or laptop bag and feels nice to the touch. Plus, it bends easily for connecting to devices in tight spaces or around obstacles.

Provides Extra Protection Against Certain Bacteria

The molded connectors and jacket are constructed using an antibacterial material that is effective in inhibiting Escherichia coli (E. coli) and Staphylococcus aureus (staph). This added protection makes this Safe-It™ cable an ideal solution for medical facilities, schools, businesses, restaurants/kitchens and anywhere else that needs extra protection against bacteria.

Light Blue Jacket Helps Avoid Misidentification That Can Cause Costly Downtime

The USB cable has a light blue jacket, which is easy to identify quickly in a crowded charging station and helps prevent the cable from becoming accidentally disconnected.

Specifications

OVERVIEW	
UPC Code	037332276773
Technology	USB; USB 2.0 (High Speed)
Cable Type	Passive

Highlights

- Soft, flexible silicone jacket allows easy bending and avoids messy tangling
- Constructed with antibacterial material proven effective in inhibiting E. coli and staph
- Supports USB 2.0 speeds up to 480 Mbps to ensure efficient charges and data transfers
- Supports 60W power output for charging, syncing and powering mobile devices
- Light blue jacket permits fast, easy identification in a crowded charging station

Applications

- Charge and sync your MacBook, Chromebook or other USB-C device from a USB computer or wall charger up to 6-ft. away
- Transfer data between an external hard drive and your USB-C notebook or computer
- Provide extra protection against bacteria to give cable installers and IT personnel peace of mind during installation

System Requirements

- Device or charger with USB-A port
- Device with USB-C or Thunderbolt 3 port

Package Includes

U038AB-006-S-LB USB-A to USB-C Cable (M/M), Light Blue, 6 ft. (1.8 m)

INPUT	
Maximum Input Amps	3
Maximum Input Watts	60
PHYSICAL	
Color	Light Blue
Material of Construction	PVC
Cable Jacket Color	Light Blue
Connector Color	Light Blue
Cable Jacket Material	Silicone
Cable Jacket Rating	FT2
Cable Outer Diameter (OD)	4.1 mm
Cable Length (ft.)	6
Cable Length (m)	1.83
Cable Length (in.)	72
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.19
Shipping Weight (kg)	0.09
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
Unit Packaging Type	Polybag
ENVIRONMENTAL	
Operating Temperature Range	14° to 140°F (-10° to 60°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Operating Humidity Range	10% to 85% RH, Non-Condensing
Storage Humidity Range	10% to 85% RH, Non-Condensing
Power Provided to Connected Device(s)	60W (20V/3A)
CONNECTIONS	
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	USB C (MALE)
Connector Plating	Nickel
Contact Plating	Nickel
FEATURES & SPECIFICATIONS	

USB Specification	USB 2.0 (up to 480 Mbps)
Antibacterial	Yes
IP68 Rated	No
Angled Plug	No
STANDARDS & COMPLIANCE	
Product Compliance	CE (Europe); REACH; RoHS; UKCA
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty