

USB-A to USB-C Cable, USB 2.0, 3A Rating, USB-IF Certified, (M/M), 13 ft. (3.96 m)

MODEL NUMBER: U038-C13



USB-A to USB-C cable connects a smartphone or other USB-C device to the USB-A port on your computer, wall charger or car charger.

Features

USB Type-A to USB Type-C Cable Connects a USB-C Mobile Device to Your Computer This 13-ft. (3.96 m) USB Type-A to USB Type-C cable allows you to connect a device with a USB-C or Thunderbolt 3 port to a USB-enabled computer, charger, hard drive, hub or other peripheral for the purpose of charging, powering, syncing or transferring data. It is compatible with any device with a USB-C or Thunderbolt 3 port, including tablets, smartphones, MacBooks, Ultrabooks and Chromebooks.

PD Charging Cable Charges Devices and Transfers Data at USB 2.0 Speeds The USB Type-A to USB Type-C cable supports USB 2.0 data transfer speeds up to 480 Mbps. The Power Delivery cable also provides power output up to 3 amps (60 watts), which is more than sufficient for charging, syncing and powering compatible devices. The cable is backward compatible with previous USB generations, allowing you to use it with older equipment.

Reversible USB-C Connector Attaches in Either Direction Unlike traditional USB cables that connect in only one direction, the reversible USB-C male connector plugs into a USB-C or Thunderbolt 3 port in either direction for a fumble-free connection every time.

USB-IF Certification Ensures Rigorous Testing and Top-of-the-Line Performance This USB Type-A to USB Type-C cable meets the high standards of USB-IF (USB Implementers Forum, Inc.), a non-profit organization consisting of companies that developed the USB specification. Receiving USB-IF certification means the U038-C13 meets the industry's highest environmental, mechanical and electrical standards. It operates with your USB peripherals, adapters and cables with top efficiency and safety.

Highlights

- Certified by USB-IF to ensure highest-grade construction and performance
- Supports USB 2.0 speeds up to 480 Mbps to ensure efficient data transfers
- Power Delivery cable provides 3A (60W) power output for charging mobile devices
- Reversible USB-C plug connects in either direction for immediate no-fuss use
- USB-A to USB-C cable compatible with all USB-A, USB-C and Thunderbolt 3 devices

Applications

- Charge and sync a USB-C mobile device from a USB-A wall charger up to 13-ft. (3.96 m) away
- Transfer data between an external hard drive or flash drive and your computer or laptop

System Requirements

- Device with a USB-C or Thunderbolt 3 port
- Device with a USB-A port

Package Includes

- U038-C13 USB-A to USB-C Cable (M/M), USB-IF Certified, 13 ft. (3.96 m)

Specifications

OVERVIEW	
UPC Code	037332214928
Technology	USB 2.0 (High Speed)
Cable Type	Passive



Powering Business Worldwide

TRIPP LITE
SERIES

CONNECTIONS	
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	USB C (MALE)
Connector Plating	Nickel
Contact Plating	Gold
Connector Style	Straight
PHYSICAL	
Material of Construction	PVC
Cable Jacket Color	Black
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	4.4 mm
Cable Length (ft.)	13
Cable Length (m)	3.96
Cable Length (in.)	157
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.16
Shipping Weight (kg)	0.07
Unit Packaging Type	Polybag
ENVIRONMENTAL	
Operating Temperature Range	14° to 140°F (-10° to 60°C)
Storage Temperature Range	-4° to 158°F (-20° to 70°C)
Relative Humidity	10% to 85% RH, Non-Condensing
FEATURES & SPECIFICATIONS	
USB Specification	USB 2.0 (up to 480 Mbps)
STANDARDS & COMPLIANCE	
Product Certifications	USB-IF
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty



Powering Business Worldwide

TRIPP LITE
SERIES

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.