

## USB-C Cable (M/M) - USB 2.0, 6 ft. (1.83 m)

MODEL NUMBER: **U040-006-C**



Connect two devices with USB Type-C (USB-C) connectors, such as smartphones, tablets, Ultrabooks and computers.

### Description

The U040-006-C USB 2.0 Hi-Speed Cable connects two devices with USB-C connectors—such as smartphones, tablets, Ultrabooks and computers—or a USB-C device to a wall charger with a USB-C port. This 6-ft. (1.83 m) cable supports data transfer speeds up to 480 Mbps and power output up to 3A for fast charging of mobile devices. Unlike traditional USB cables that can be attached only one way, the reversible USB-C male connectors plug into a USB port in either direction for fast, fumble-free connection every time. Superior foil shielding provides reliable, error-free data communication. Nickel-plated molded end connectors and gold-plated copper contacts ensure superior conductivity and long life. Slim form supports evolving design trends toward smaller devices. Backward compatible with previous USB generations.

### Features

#### Supports USB 2.0

- Data transfer speeds up to 480 Mbps
- Power output up to 3A—perfect for fast charging of most mobile devices
- Backward compatible with previous USB generations

#### USB Type-C Male Connector

- Fumble-free reversible plug ensures fast, easy connection every time
- Powerful enough for smartphones, tablets, computers and other larger platforms

#### Premium Construction

- Gold-plated copper contacts and nickel-plated molded ends provide a lifetime of heavy use and superior conductivity
- Superior foil shielding offers reliable, error-free data communication
- Slim, sleek design tailored for emerging design trends toward smaller devices

## Specifications

### Highlights

- Connects two USB-C devices
- Supports USB 2.0 data transfer speeds up to 480 Mbps
- Provides power output up to 3A
- Features reversible USB-C male plugs on both ends
- Works with previous USB generations

### System Requirements

- Devices with a USB Type-C port

### Package Includes

- U040-006-C USB 2.0 Hi-Speed Cable, USB Type-C to USB Type-C M/M, 6-ft. (1.83 m)



| <b>OVERVIEW</b>                      |                                |
|--------------------------------------|--------------------------------|
| UPC Code                             | 037332190154                   |
| Technology                           | USB 2.0 (High Speed)           |
| USB Cable Type                       | Passive                        |
| <b>PHYSICAL</b>                      |                                |
| Material of Construction             | PVC                            |
| Color                                | Black                          |
| Cable Jacket Color                   | Black                          |
| Cable Jacket Rating                  | VW-1                           |
| Cable Outer Diameter (OD)            | 3.5MM                          |
| Cable Length (ft.)                   | 6                              |
| Cable Length (m)                     | 1.83                           |
| Cable Length (in.)                   | 72                             |
| Shipping Dimensions (hwd / cm)       | 17.78 x 22.86 x 1.27           |
| Shipping Dimensions (hwd / in.)      | 7.00 x 9.00 x 0.50             |
| Shipping Weight (kg)                 | 0.04                           |
| Shipping Weight (lbs.)               | 0.09                           |
| <b>ENVIRONMENTAL</b>                 |                                |
| Operating Temperature Range          | 14 to 140 F (-10 to 60 C)      |
| Storage Temperature Range            | -4 to 185 F (-20 to 85 C)      |
| Relative Humidity                    | 10% to 85%, Non-Condensing     |
| <b>CONNECTIONS</b>                   |                                |
| Side A - Connector 1                 | USB C (MALE)                   |
| Side B - Connector 1                 | USB C (MALE)                   |
| Connector Plating                    | Nickel                         |
| Contact Plating                      | Gold                           |
| <b>FEATURES &amp; SPECIFICATIONS</b> |                                |
| USB Specification                    | USB 2.0 (up to 480 Mbps)       |
| <b>STANDARDS &amp; COMPLIANCE</b>    |                                |
| Certifications                       | Tested to CE, FCC, RoHS, REACH |
| <b>WARRANTY</b>                      |                                |



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

|  |                           |
|--|---------------------------|
| Product Warranty Period<br>(Worldwide) | Lifetime limited warranty |
|--|---------------------------|

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>