

USB 2.0 Adapter Cable, USB-C to USB Micro-B (M/F), 6-in.

MODEL NUMBER: **U040-06N-MIC-F**



Convert the USB Type-C (USB-C) port on your device, tablet, laptop, ultrabook, or computer to a USB Micro-B Female port

Description

Tripp Lite's U040-06N-MIC-F 6-in. USB 2.0 Hi-Speed adapter cable converts the USB Type-C (USB-C) port on your tablet, laptop, ultrabook or computer to a USB Micro-B port, allowing for Micro-B devices to charge and sync. The USB Type-C connector is reversible, so there is no guessing on which way to plug it in...it connects in either direction! Backward compatible - can be used with older USB 1.1 applications as well. All Tripp Lite USB 2.0 cabling include superior foil shielding for reliable, error-free data communications. Features nickel plated connectors and gold plated copper contacts for superior conductivity. The cable is manufactured with molded connectors and integral strain relief for extra durability and long life.

Features

- 6-in. USB Type-C (USB-C) Male to USB Micro-B Female adapter cable
- Converts the USB Type-C port on your tablet, laptop, ultrabook, or computer to a USB Micro-B port, allowing for Micro-B devices to sync and charge
- USB Type-C connector is reversible, so there is no guessing on which way to plug it in
- Supports USB 2.0 data transfer rates up to 480Mbps
- Backward compatible with previous USB generations
- Gold plated contacts and molded ends provide a lifetime of use
- 30AWG Data Pair / 24AWG Power Pair

Specifications

Highlights

- Connect devices with a USB Micro-B port to the USB Type-C (USB-C) port on your tablet, laptop, ultrabook or computers
- USB Type-C connector is reversible, so there is no guessing on which way to plug it in

System Requirements

- A device with a Micro-B connector
- A tablet, laptop, ultrabook or computer with an available USB Type-C (USB-C) port

Package Includes

- USB 2.0 Hi-Speed Adapter Cable, USB Type-C (USB-C) Male to USB Micro-B Female, 6-in.



OVERVIEW	
UPC Code	037332189226
Technology	USB 2.0 (High Speed); USB
INPUT	
Cable Length (ft.)	0.5
Cable Length (m)	0.2
Cable Length (in.)	6
PHYSICAL	
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	3.0MM
Color	Black
Material of Construction	PVC
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Weight (kg)	0.02
Shipping Weight (lbs.)	0.04
ENVIRONMENTAL	
Operating Temperature Range	14 to 140 F (-10 to 60 C)
Storage Temperature Range	-4 to 185 F (-20 to 85 C)
Relative Humidity	10% to 85%, Non-Condensing
CONNECTIONS	
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	MICRO-USB B (FEMALE)
Connector Plating	Nickel
Contact Plating	Gold
FEATURES & SPECIFICATIONS	
USB Specification	USB 2.0 (up to 480 Mbps)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>