

## Safe-IT USB-C Antibacterial Cable, USB 2.0, Ultra Flexible (M/M), Light Blue, 6 ft. (1.83 m)

MODEL NUMBER: U040AB-006-CSLB



USB cable with antibacterial material connects a smartphone or other USB-C device to the USB-C port on your computer, charger or power bank.

### Features

#### USB-C Cable Connects Devices for Charging or Transferring Data

This USB cable (M/M) is compatible with any device with a USB-C or Thunderbolt 3 port, including a MacBook Pro, iPad, iMac, Chromebook or Windows laptop. It allows you to connect your notebook computer to a docking station, your Apple or Android device to a wall charger or power bank, or an external hard drive to a PC or tablet, to name just a few valuable uses for the cable.

#### Innovative Soft Cable Jacket Prevents Tangles, Allows Flexible Bends

Very flexible for convenient on-the-go connections, this ultra-soft silicone-layered jacket avoids nasty tangles in your backpack or laptop bag and feels nice to the touch. Plus, it bends easily for connecting to devices in tight spaces or around obstacles.

#### PD Charging Cable Supports up to 60W for Syncing and Charging Mobile Devices

The Power Delivery cable provides power output up to 20V 3A (60W), which is sufficient for fast charging, syncing and powering most smartphones and other mobile devices. It also supports USB 2.0 data transfer rates up to 480 Mbps. The USB-C to USB-C cable is backward compatible with previous USB generations, allowing you to use it with older equipment.

#### Provides Extra Protection Against Certain Bacteria

The molded connectors and jacket are constructed using an antibacterial material that is effective in inhibiting Escherichia coli (E. coli) and Staphylococcus aureus (staph). This added protection makes this Safe-It™ cable an ideal solution for medical facilities, schools, businesses, restaurants/kitchens and anywhere else that needs extra protection against bacteria.

#### Light Blue Jacket Helps Avoid Misidentification That Can Cause Costly Downtime

The USB cable has a light blue jacket, which is easy to identify quickly in a crowded docking station or USB hub and helps prevent the cable from becoming accidentally disconnected.

## Specifications

### Highlights

- Soft, flexible silicone jacket allows easy bending and avoids messy tangling
- Constructed with antibacterial material proven effective in inhibiting E. coli and staph
- Supports USB 2.0 speeds up to 480 Mbps to ensure efficient charges and data transfers
- Power Delivery cable supports 20V 3A (60W) power output for charging host device
- Light blue jacket permits fast, easy identification in a crowded docking station or hub

### Applications

- Charge and sync a USB-C or Thunderbolt 3 mobile device from a USB-C wall charger up to 6-ft. away
- Transfer data between an external hard drive or flash drive and your laptop or computer
- Provide extra protection against bacteria to give cable installers and IT personnel peace of mind during installation

### System Requirements

Devices with USB-C or Thunderbolt 3 ports

### Package Includes

U040AB-006-CSLB USB-C to USB-C Cable (M/M), Light Blue, 6 ft. (1.8 m)

| OVERVIEW                                       |                             |
|--|-----------------------------|
| UPC Code                                       | 037332276780                |
| Technology                                     | USB                         |
| Cable Type                                     | Passive                     |
| INPUT  |                             |
| Maximum Input Amps                             | 3                           |
| Maximum Input Watts                            | 60                          |
| POWER  |                             |
| USB Power Delivery (PD) Charging Support       | Yes                         |
| USB Power Delivery (PD) Charging Specification | 3.0                         |
| PHYSICAL                                       |                             |
| Cable Jacket Color                             | Light Blue                  |
| Connector Color                                | Light Blue                  |
| Cable Jacket Material                          | Silicone                    |
| Cable Jacket Rating                            | FT2                         |
| Cable Outer Diameter (OD)                      | 4.1MM                       |
| Cable Length (ft.)                             | 6                           |
| Cable Length (m)                               | 1.83                        |
| Cable Length (in.)                             | 72                          |
| Cable Length (cm)                              | 91.4                        |
| Shipping Dimensions (hwd / in.)                | 9.00 x 7.00 x 0.50          |
| Shipping Dimensions (hwd / cm)                 | 22.86 x 17.78 x 1.27        |
| Shipping Weight (lbs.)                         | 0.17                        |
| Shipping Weight (kg)                           | 0.08                        |
| Unit Dimensions (hwd / in.)                    | 0.000 x 0.000 x 0.000       |
| Unit Packaging Type                            | Polybag                     |
| ENVIRONMENTAL                                  |                             |
| Operating Temperature Range                    | 14° to 140°F (-10° to 60°C) |
| Storage Temperature Range                      | -4° to 140°F (-20° to 60°C) |
| Operating Humidity Range                       | 10% to 85%, Non-Condensing  |
| Storage Humidity Range                         | 10% to 85%, Non-Condensing  |

|                                       |                                |
|---------------------------------------|--------------------------------|
| Power Provided to Connected Device(s) | 60W (20V/3A)                   |
| <b>CONNECTIONS</b>                    |                                |
| Side A - Connector 1                  | USB C (MALE)                   |
| Side B - Connector 1                  | USB C (MALE)                   |
| Connector Plating                     | Nickel                         |
| Contact Plating                       | Nickel                         |
| <b>FEATURES &amp; SPECIFICATIONS</b>  |                                |
| USB Specification                     | USB 2.0 (up to 480 Mbps)       |
| Antibacterial                         | Yes                            |
| IP68 Rated                            | No                             |
| Angled Plug                           | No                             |
| <b>STANDARDS &amp; COMPLIANCE</b>     |                                |
| Product Compliance                    | CE (Europe); REACH; RoHS; UKCA |
| <b>WARRANTY &amp; SUPPORT</b>         |                                |
| Product Warranty Period (Worldwide)   | Lifetime limited warranty      |