

USB 2.0 A to B Active Repeater Cable (M/M), 36 ft. (10.97 m)

MODEL NUMBER: **U042-036**



Locate a printer or other USB peripheral 36-ft. from your computer.

Features

- Connect a computer to a printer or other USB device up to 36-ft. away
- High-Speed USB 2.0 and USB 1.1 compatible
- Active repeater maintains 480Mbps signal integrity
- USB "A" to USB "B" connections
- Windows 98/ME/2000/XP/Vista/WIN7/8/10 and MAC compatible
- Cable length: 36-ft. Weight: 1 lb.
- Repeater Pod dimension: 16.75 x 57.3 x 31.7 (mm.) / 0.7 x 2.3 x 1.3 (in.)
- The U042-036 provides up to 150mA of power to the connected device. If your device requires more than 150mA of power, it will either need to have its own power supply; or, to be plugged into a powered USB 2.0 hub (such as U222-007-R) that is connected to the U042-036.

Specifications

OVERVIEW	
UPC Code	037332138712
Technology	USB 2.0 (High Speed)
Cable Type	Active
CONNECTIONS	
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	USB B (MALE)
Connector Style	Straight

Highlights

- 36-ft. USB A-B Active Cable
- Overcomes the 5-meter USB barrier
- Built-in repeater maintains high-speed USB 2.0 signal quality

System Requirements

- A USB 2.0 port and USB 2.0 device (with type B jack) are required to meet USB 2.0 speeds. A USB 1.1 port and/or device can be used, but you will not be able to achieve USB 2.0 speeds.
- The U042-036 provides up to 150mA of power to the connected device. If your device requires more than 150mA of power, it will either need to have its own power supply; or, to be plugged into a powered USB 2.0 hub (such as U222-007-R) that is connected to the U042-036.

Package Includes

- 36-ft. Hi-Speed USB 2.0 Active Cable



Powering Business Worldwide



PHYSICAL	
Cable Jacket Color	Black
Cable Length (ft.)	36
Cable Length (m)	10.98
Shipping Dimensions (hwd / in.)	9.10 x 10.60 x 0.10
Shipping Dimensions (hwd / cm)	23.11 x 26.92 x 0.25
Shipping Weight (lbs.)	0.77
Shipping Weight (kg)	0.35
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.