

USB to DC Power Cable - M/M, USB-A to 3.5 x 1.35 mm DC Barrel Plug, 3 ft. (0.91 m)

MODEL NUMBER: U152-003-3P5



USB to 5V DC power cable powers a 5V DC device using your computer's USB port instead of the device's power supply.

Features

USB to DC Adapter Charges 5V DC Peripherals via USB Port Now you can power up your external 5V DC devices without having to carry around a bulky DC transformer or find room for it in your surge protector or power strip. This USB to 5V DC power cable connects to your computer or laptop's USB-A port to provide power to operate your device. You can also connect your device to a USB wall charger or car charger. It's recommended for powering devices with a 3.5 x 1.35 millimeter 5V DC barrel jack, such as external hard drives, wireless routers, Bluetooth speakers and credit card readers.

Lifetime Warranty The U152-003-3P5 is backed by a lifetime warranty, ensuring reliability and performance.

Specifications

OVERVIEW	
UPC Code	037332212986
Cable Type	Passive
CONNECTIONS	
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	3.5mm x 1.35mm (5V DC Barrel)
Connector Plating	Nickel
PHYSICAL	
Color	Black
Material of Construction	PVC

Highlights

- USB to DC adapter powers 5V DC devices through your PC or laptop's USB-A port
- Avoid carrying bulky transformers in your laptop bag or blocking power strip outlets
- Polarity: positive tip, negative sleeve
- Recommended for devices with 3.5 x 1.35 mm barrel connector with positive center pin

Applications

- Power an external hard drive via USB port or hub to avoid blocking outlets on your surge protector with a bulky transformer
- Connect a credit card reader to your laptop to ring up sales
- Charge your wireless speaker through your computer's USB port instead of plugging it into a wall socket

Package Includes

- U152-003-3P5 USB to DC Power Cable – M/M, USB-A to 3.5 x 1.35 mm DC Barrel Plug, 3 ft.



Powering Business Worldwide

TRIPP LITE
SERIES

Cable Jacket Color	Black
Cable Jacket Rating	CMR
Cable Outer Diameter (OD)	5.0+-0.15mm
Wire Gauge (AWG)	20
Cable Length (ft.)	3
Cable Length (m)	0.91
Shipping Dimensions (hwd / in.)	5.00 x 4.00 x 0.50
Shipping Dimensions (hwd / cm)	12.70 x 10.16 x 1.27
Shipping Weight (lbs.)	0.11
Shipping Weight (kg)	0.05
Unit Packaging Type	Polybag
ENVIRONMENTAL	
Operating Temperature Range	5 ~ 50C (41 ~ 122F)
Storage Temperature Range	-25 ~ 70C (-13 ~ 158F)
Operating Humidity Range	20% ~ 85% RH
Storage Humidity Range	0% ~ 90% RH
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.