

## USB to DC Power Cable – M/M, USB-A to 3.5 x 1.35 mm DC Barrel Plug, 3 ft.

MODEL NUMBER: **U152-003-3P5**



USB to 5V DC power cable powers a 5V DC device using your computer's USB port instead of the device's power supply.

### Features

**USB to DC Adapter Charges 5V DC Peripherals via USB Port** Now you can power up your external 5V DC devices without having to carry around a bulky DC transformer or find room for it in your surge protector or power strip. This USB to 5V DC power cable connects to your computer or laptop's USB-A port to provide power to operate your device. You can also connect your device to a USB wall charger or car charger. It's recommended for powering devices with a 3.5 x 1.35 millimeter 5V DC barrel jack, such as external hard drives, wireless routers, Bluetooth speakers and credit card readers.

**Lifetime Warranty** The U152-003-3P5 is backed by a lifetime warranty, ensuring reliability and performance.

### Highlights

- USB to DC adapter powers 5V DC devices through your PC or laptop's USB-A port
- Avoid carrying bulky transformers in your laptop bag or blocking power strip outlets
- Polarity: positive tip, negative sleeve
- Recommended for devices with 3.5 x 1.35 mm barrel connector with positive center pin

### Applications

- Power an external hard drive via USB port or hub to avoid blocking outlets on your surge protector with a bulky transformer
- Connect a credit card reader to your laptop to ring up sales
- Charge your wireless speaker through your computer's USB port instead of plugging it into a wall socket

### Package Includes

- U152-003-3P5 USB to DC Power Cable – M/M, USB-A to 3.5 x 1.35 mm DC Barrel Plug, 3 ft.

## Specifications

OVERVIEW	
UPC Code	037332212986
Technology	USB



<b>INPUT</b>	
Cable Length (ft.)	3
Cable Length (m)	1
<b>PHYSICAL</b>	
Cable Jacket Rating	CMR
Cable Outer Diameter (OD)	5.0+-0.15mm
Color	Black
Material of Construction	PVC
Shipping Dimensions (hwd / cm)	12.70 x 10.16 x 1.27
Shipping Dimensions (hwd / in.)	5.00 x 4.00 x 0.50
Shipping Weight (kg)	0.05
Shipping Weight (lbs.)	0.11
Unit Packaging Type	Polybag
Wire Gauge (AWG)	20
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	5 ~ 50C (41 ~ 122F)
Storage Temperature Range	-25 ~ 70C (-13 ~ 158F)
Operating Humidity Range	20% ~ 85% RH
Storage Humidity Range	0% ~ 90% RH
<b>CONNECTIONS</b>	
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	3.5mm x 1.35mm (5V DC Barrel)
Connector Plating	Nickel
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	RoHS, REACH
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>