

2-Port USB to DB9 Serial FTDI Adapter Cable with COM Retention (M/M), 6 ft. (1.83 m)

MODEL NUMBER: U209-006-2



Connect 2 devices with 9-pin RS-232 serial ports to the USB-A port on your computer, laptop or tablet. Recommended for connecting modems, digital cameras, PDAs and ISDN terminals.

Features

Connects 2 DB9 Devices to a USB-A Device

- Recommended for connecting a modem, digital camera, PDA or ISDN terminal to your computer, laptop or tablet
- Supports data transfer speeds up to 225 Kbps—twice as fast as a built-in serial port
- No external power source required
- Portable 6 ft. design fits perfectly into laptop bag
- COM retention for automatic reassigning of COM values to ports in case of disconnection or reboot
- Integrated FTDI FT232RL chipset

First-Rate Construction for Superior Signal Transfer

- Premium foil and braid shielding for EMI/RFI noise protection
- Molded nickel-plated connectors with gold-plated contacts for optimal signal quality
- Integral strain relief for long life
- Flexible PVC jacket easy to install in tight spaces

Broad Compatibility

- Compatible with Windows, Mac and Linux operating systems

Specifications

OVERVIEW	
UPC Code	037332198303

Highlights

- Supports data transfer speeds up to 225 Kbps
- Premium foil and braid shielding reduces EMI/RFI line noise
- Compatible with Windows®, Mac® and Linux® devices
- No external power source required
- Integrated FTDI FT232RL chipset

System Requirements

- Computer or other device with available USB port and Windows XP or later, Mac OS X 10.3 and later, or Linux operating system

Package Includes

- U209-006-2 2-Port USB to DB9 Serial FTDI Adapter Cable (M/M), 6 ft.
- Driver CD
- Owner's manual



Technology	Serial (RS232); USB
INPUT	
Bus Powered	Yes
PHYSICAL	
Color	Black
Cable Jacket Rating	VW-1
Cable Length (ft.)	6
Cable Length (m)	1.8
Material of Construction	PVC
Shipping Dimensions (hwd / cm)	5.08 x 12.45 x 12.70
Shipping Dimensions (hwd / in.)	2.00 x 4.90 x 5.00
Shipping Weight (kg)	0.18
Shipping Weight (lbs.)	0.40
Unit Packaging Type	Box
Unit Weight (kg)	0.06
Unit Weight (lbs.)	0.13
ENVIRONMENTAL	
Operating Temperature Range	32 to 104 F (0 to 40 C)
Storage Temperature Range	14 to 131 F (-10 to 55 C)
Relative Humidity	5% to 90% RH, Non-Condensing
BTUs	1.7 BTU/Hr
Power Consumption (Watts)	0.50
CONNECTIONS	
Ports	2
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	(2) DB9 (MALE)
Connector Plating	Nickel
FEATURES & SPECIFICATIONS	
USB Specification	USB 2.0 (up to 480 Mbps)
Driver Required	Yes
STANDARDS & COMPLIANCE	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Certifications	Tested to CE, FCC, RoHS, REACH, WEEE
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>