

USB-C to RJ45 Serial Rollover Cable (M/M) - Cisco Compatible, 250 Kbps, 6 ft. (1.8 m)

MODEL NUMBER: U209-006-RJ45XC



Connects your computer or laptop's USB-C port to a Cisco modem, router, firewall, switch or other serial-based Cisco device with an RJ45 console port.

Features

Connects Your Computer's USB-C Port to a Cisco Device

Directly connect the RJ45 console port on your Cisco modem, router, firewall, switch or other serial-based Cisco device to the USB-C port on your computer or laptop. The U209-006-RJ45XC supports data transfer rates up to 250 Kbps, as well as remote wake-up and power management. It is compatible with Windows, macOS and Linux.

Filtering EMI/RFI Line Noise Helps Your Equipment Perform Better

This Cisco-compatible cable blocks disruptive EMI (electromagnetic interference) and RFI (radio frequency interference) line noise that can disturb your network equipment and inflict hardware damage or data loss. Premium double-shielding eliminates crosstalk and helps your connected components perform better and last longer.

Specifically Designed for Cisco Equipment

The serial cable is compatible with both older and current Cisco models. It requires no external power or additional adapters. You may download and install the necessary driver from the product page at tripplite.com/support (see the included owner's manual for directions).

Specifications

OVERVIEW	
UPC Code	037332268655
Technology	Serial; USB
POWER	
USB Power Delivery (PD) Charging Support	No

Highlights

- Supports data transfer rates up to 250 Kbps
- Supports remote wake-up and power management
- Premium double-shielded cable eliminates crosstalk and reduces EMI/RFI interference
- Compatible with Windows, macOS and Linux operating systems
- Designed for Cisco equipment with no adapters or external power required

System Requirements

- Computer with USB-C port and Windows, macOS or Linux operating system
- Cisco device with RJ45 console port

Package Includes

- U209-006-RJ45XC USB-C to RJ45 Serial Rollover Cable, M/M, 6 ft. (1.8 m)
- Owner's manual



PHYSICAL	
Color	Black
Cable Jacket Color	Blue
Connector Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	RJ45: 5.5MM; USB: 4.7MM
Cable Length (ft.)	6
Cable Length (m)	1.83
Cable Length (in.)	72
Unit Packaging Type	Box
Unit Weight (lbs.)	0.2425
Unit Weight (kg)	0.11
ENVIRONMENTAL	
Operating Temperature Range	32 TO 104 F (0 TO 40 C)
Storage Temperature Range	-4 TO 140 F (-20 TO 60 C)
Operating Humidity Range	0% TO 90% RH, NON-CONDENSING
Storage Humidity Range	0% TO 90% RH, NON-CONDENSING
COMMUNICATIONS	
Network Compatibility	250 Kbps
CONNECTIONS	
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	RJ45 (MALE)
FEATURES & SPECIFICATIONS	
Driver Required	Yes
Remote Wakeup Support	Yes
STANDARDS & COMPLIANCE	
Certifications	CE, FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:
<https://www.tripplite.com/products/product-certification-agencies>