



# 4-Port USB 2.0 Ultra-Mini Compact Hub with Power Adapter

MODEL NUMBER: U222-004-R









#### **Features**

- USB2.0 Hub 4-Port
- Supports all data transfer rates up to 480Mbps
- Compact design with built-in cable (6-in.), perfect for travel
- Plug-and-play/hot-swappable allows you to add or remove a device at any time
- Diagnostic LEDs indicate power and port status
- Bus-powered or self-powered
- All four ports support USB Battery Charging (BC) specification v1.2, providing up to 1.5A for fast charging of mobile devices
- Includes External Power Supply with NEMA 1-15P Plug (Input: 100-240V, 50/60Hz, 0.35A; Output: 5V, 2A)
- Includes a 2.6ft USB-A to Micro-B USB 2.0 cable to connect the U222-004-R to the External Power Supply
- Compatible with all major operating systems

#### **Highlights**

- Link multiple USB devices to 1 computer with ultra-compact bub
- Meets or Exceeds USB 2.0 Specifications
- Includes External Power Supply with NEMA 1-15P Plug (Input: 100-240V, 50/60Hz, 0.35A; Output: 5V, 2A)
- Includes a 2.6-ft. (0.79 m) USB-A to Micro-B USB 2.0 Cable
- All four ports support USB Battery Charging (BC) specification v1.2, providing up to 1.5A for fast charging of mobile devices

### **Package Includes**

- U222-004-R USB2.0 4-Port Ultra-Mini Hub
- External Power Supply with NEMA 1-15P Plug (Input: 100-240V, 50/60Hz, 0.35A; Output: 5V, 2A)
- USB-A to Micro-B USB 2.0 Cable, 2.6-ft. (0.79 m)

## **Specifications**

OVERVIEW		
UPC Code	037332118127	
Product Type	Hub	
Technology	USB 2.0 (High Speed)	
Host Connector	USB A (MALE)	
VIDEO		





Number of Monitors Supported	0	
Extended Mode	No	
Mirror Mode	No	
DATA		
Data Ports	(4) USB A (FEMALE)	
Data Ports Details	(4) USB-A - USB 2.0	
INPUT		
AC Power Adapter Input Specs (V / Hz / A)	100-240V / 50/60Hz / 0.35A	
AC Power Adapter Output Specs (V / A)	5V / 2A	
Voltage Compatibility (VAC)	100; 110; 120; 125; 127; 200; 208; 220; 230; 240	
POWER		
AC Adapter	Input: 100-240V, 50/60Hz, 0.35A; Output: 5V, 2A	
CONNECTIONS		
Number of Ports	4	
Side A - Connector 1	USB A (MALE)	
Side B - Connector 1	(4) USB A (FEMALE)	
CHARGING		
Charging Ports	(4) USB-A: 5V 1.5A (7.5W)	
Charging Ports Details	Any of the 4 ports	
Charging Ports / Amps	(4) 1.5A	
PHYSICAL		
Color	Black	
Material of Construction	Plastic	
Cable Length (ft.)	0.5	
Cable Length (m)	0.15	
Shipping Dimensions (hwd / in.)	1.00 x 4.00 x 5.10	
Shipping Dimensions (hwd / cm)	2.54 x 10.16 x 12.95	
Shipping Weight (lbs.)	0.30	
Shipping Weight (kg)	0.14	
FEATURES & SPECIFICATIONS		
USB Hub Ports	Yes	





Number of USB Hub Ports	4	
USB Specification	USB 2.0 (up to 480 Mbps)	
STANDARDS & COMPLIANCE		
TAA Compliant Option	N	
Product Certifications	NOM (Mexico)	
Product Compliance	RoHS; REACH; WEEE; FCC (USA)	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	3-year limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.