

4-Port USB 2.0 USB over Cat5 Hub with 3 local Ports and 1 Remote Port, TAA

MODEL NUMBER: U224-1R4-R



Description

The U224-1R4-R is a kit that includes a 3-port USB 2.0 local transmitter unit and a 1-port USB 1.1 remote receiver unit. Connect up to three USB 2.0 devices to the local transmitter, while extending an additional USB 1.1 peripheral up to 150 feet (45.7 meters) from your computer. Simply plug the transmitter into the USB port on your computer, connect your USB peripherals and run Cat5e/Cat6 cable up to 150 feet to the remote receiver unit and connected device. Plug-and-play; no software or drivers required. Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

Features

- Local transmitter unit features 3 USB 2.0 ports
- Remote receiver unit features 1 USB 1.1 port
- Locate a USB 1.1 peripheral up to 150-ft. (45.72 m) from your computer
- Uses readily available Cat5e/Cat6 patch cable
- Plug-and-play; no software or drivers required
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

OVERVIEW	
UPC Code	037332146694
Product Type	Hub
Technology	USB 2.0 (High Speed)
Host Connector	USB A (MALE)
VIDEO	

Highlights

- Local transmitter unit features 3 USB 2.0 ports
- Remote receiver unit features 1 USB 1.1 port
- Locate a USB 1.1 peripheral up to 150-ft. (45.72 m) from your computer
- Plug-and-play; no software or drivers required
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Package Includes

- 3-port USB 2.0 local transmitter unit
- 1-port USB 1.1 remote receiver unit
- External Power Supply with NEMA 1-15P Plug (Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 2A)
- Owner's manual

Number of Monitors Supported	0
Extended Mode	No
Mirror Mode	No
DATA	
Data Ports	(4) USB A (FEMALE)
Data Ports Details	(4) USB-A - USB 2.0
POWER	
AC Adapter	Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 2A
PHYSICAL	
Color	Black
Receiver Unit Height (in.)	0.9
Receiver Unit Width (in.)	1.8
Receiver Unit Depth (in.)	2.6
Shipping Dimensions (hwd / in.)	2.30 x 5.90 x 8.90
Shipping Dimensions (hwd / cm)	5.84 x 14.99 x 22.61
Shipping Weight (lbs.)	0.80
Shipping Weight (kg)	0.36
Transmitter Unit Depth (in.)	3.3
Transmitter Unit Height (in.)	0.9
Transmitter Unit Width (in.)	2.4
CONNECTIONS	
Number of Ports	4
Side A - Connector 1	USB A (MALE)
Side A - Connector 2	RJ45 (FEMALE)
Side B - Connector 1	(4) USB A (FEMALE)
Side B - Connector 2	RJ45 (FEMALE)
FEATURES & SPECIFICATIONS	
USB Hub Ports	Yes
Number of USB Hub Ports	4
USB Specification	USB 2.0 (up to 480 Mbps)
STANDARDS & COMPLIANCE	



1000 Eaton Boulevard
Cleveland, OH 44122
United States

TAA Compliant Option	Y
Product Compliance	Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty



© 2023 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.