



4-Port USB 2.0 Hub

MODEL NUMBER: U225-004-R









Highlights

- Supports Hi-Speed data transfer rates up to 480 Mbps
- Meets or Exceeds USB 2.0 Specifications
- Supports USB 2.0 spec up to 500mA per port
- Hot Pluggable
- Includes 4ft USB 2.0 Computer to Hub cable

System Requirements

 A Windows, Mac or Linux computer with an available USB port

Package Includes

- U225-004-R
- 4ft USB Mini-B 5-Pin Male to USB A Male device cable

Description

The U225-004-R 4-port USB 2.0 Hub allows you to attach multiple USB devices to a single USB port on your computer. The hub supports all three data transfer speeds: low speed (1.5 Mbps), full speed (12 Mbps) and Hi-Speed (480 Mbps). Includes four-foot USB 2.0 Computer to Hub cable (A-B).

Features

- USB 2.0 and 1.1 compliant
- Compact desktop design (4"W x 2.5"D x .625"H)
- Does not require external power, software, or complicated set-up procedures
- Supports USB 2.0 spec up to 500mA per port
- On bus-power, 500mA from the USB 2.0 computer port is shared between the hub ports
- Plug & Play and Hot Swap capability
- Compatible with Windows, Mac and Linux

Specifications

OVERVIEW		
UPC Code	037332116505	
Product Type	Hub	
	USB 2.0 (High Speed)	
Technology Host Connector	USB A (MALE)	
HOST COTTRECTOR	USB A (MALE)	
VIDEO		
Number of Monitors Supported	0	
Extended Mode	No	
Mirror Mode	No	





DATA	
Data Ports	(4) USB A (FEMALE)
Data Ports Details	(4) USB-A - USB 2.0
INPUT	
Voltage Compatibility (VAC)	100; 110; 120; 127; 200; 208; 220; 230; 240
Bus Powered	Yes
POWER	
Power Source Type	USB
CONNECTIONS	
Number of Ports	4
Side A - Connector 1	USB MINI-B 5-PIN (FEMALE)
Side B - Connector 1	(4) USB A (FEMALE)
PHYSICAL	
Color	Black; Silver
Material of Construction	PVC
Shipping Dimensions (hwd / in.)	5.00 x 2.00 x 5.20
Shipping Weight (lbs.)	0.30
Shipping Weight (kg)	0.14
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
Unit Packaging Type	Clamshell
Unit Weight (lbs.)	0.24
Unit Weight (kg)	0.11
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	14° to 131°F (-10° to 55°C)
Relative Humidity	5% to 90% RH, Non-Condensing
BTUs	51.2 BTU/Hr
Power Provided to Connected Device(s)	5V 0.5A (2.5W) Output per USB port
FEATURES & SPECIFICATIONS	
Over Current Protection	Yes
USB Hub Ports	Yes





Number of USB Hub Ports	4	
USB Specification	USB 2.0 (up to 480 Mbps)	
Driver Required	No	
STANDARDS & COMPLIANCE		
TAA Compliant Option	N	
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	3-year limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.