

4-Port USB 2.0 Hub

MODEL NUMBER: **U225-004-R**



Description

Tripp Lite's U225-004-R 4-port USB 2.0 Hub allows you to attach multiple USB devices to a single USB port on your computer. The hub supports all three data transfer speeds: low speed (1.5 Mbps), full speed (12 Mbps) and Hi-Speed (480 Mbps). Includes 4 ft USB 2.0 Computer to Hub cable (A-B).

Features

- USB 2.0 and 1.1 compliant
- Compact desktop design (4"W x 2.5"D x .625"H)
- Does not require external power, software, or complicated set-up procedures
- Supports USB 2.0 spec up to 500mA per port
- On bus-power, 500mA from the USB 2.0 computer port is shared between the hub ports
- Plug & Play and Hot Swap capability
- Compatible with Windows, Mac and Linux

Specifications

OVERVIEW	
UPC Code	037332116505
Product Type	Hub
Over Current Protection	Yes
Technology	USB; USB 2.0 (High Speed)
Host Connector	USB A (MALE)
VIDEO	

Highlights

- Supports Hi-Speed data transfer rates up to 480 Mbps
- Meets or Exceeds USB 2.0 Specifications
- Supports USB 2.0 spec up to 500mA per port
- Hot Pluggable
- Includes 4ft USB 2.0 Computer to Hub cable

System Requirements

- A Windows, Mac or Linux computer with an available USB port

Package Includes

- U225-004-R
- 4ft USB Mini-B 5-Pin Male to USB A Male device cable



Number of Monitors Supported	0
Extended Mode	No
Mirror Mode	No
DATA	
Data Ports	(4) USB A (FEMALE)
Data Ports Detail	(4) USB-A - USB 2.0
INPUT	
Voltage Compatibility (VAC)	100; 110; 120; 127; 200; 208; 220; 230; 240
Bus Powered	Yes
PHYSICAL	
Color	Black; Silver
Material of Construction	PVC
Shipping Dimensions (hwd / in.)	5.00 x 2.00 x 5.20
Shipping Weight (kg)	0.14
Shipping Weight (lbs.)	0.30
Unit Dimensions (hwd / in.)	0.6 x 4 x 2.5
Unit Packaging Type	Clamshell
Unit Weight (kg)	0.11
Unit Weight (lbs.)	0.24
ENVIRONMENTAL	
Operating Temperature Range	32 to 104 F (0 to 40 C)
Storage Temperature Range	14 to 131 F (-10 to 55 C)
Relative Humidity	5% to 90% RH, Non-Condensing
BTUs	51.2 BTU/Hr
Power Provided to Connected Device(s)	5V 0.5A (2.5W) Output per USB port
CONNECTIONS	
Ports	4
Side A - Connector 1	USB MINI-B 5-PIN (FEMALE)
Side B - Connector 1	(4) USB A (FEMALE)
FEATURES & SPECIFICATIONS	
USB Specification	USB 2.0 (up to 480 Mbps)



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Driver Required	No
STANDARDS & COMPLIANCE	
Certifications	Tested to CE, FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>