

A CD is no longer included with the U244-001-VGA-R. In order to install the proper drivers, please visit <https://www.displaylink.com/downloads>.

## USB 2.0 to VGA Dual-Monitor Adapter, 128 MB SDRAM, 1920 x 1080 (1080p) @ 60 Hz

MODEL NUMBER: **U244-001-VGA-R**



Connect a VGA monitor or projector to the USB 2.0 port of your computer or laptop. Use up to 6 adapters to connect up to 6 additional displays to a source. Ideal for multitasking, presentations and editing documents.

### Description

The U244-001-VGA-R USB 2.0 to VGA Dual-Monitor Adapter displays video on a VGA monitor or projector via your computer or laptop's USB 2.0 port. You can extend video from your primary display to another, duplicate the same video on both displays or change the second display to your primary display. The adapter is an ideal tool for multitasking, viewing large spreadsheets, editing documents, giving presentations at trade shows or watching movies and playing games on large screens. You can add up to six U244-001-VGA-R adapters, each attached to its own USB 2.0 port, to connect a total of seven displays to the video source. Adding or removing a monitor is easy—no need to reboot the system afterward. No external power supply is necessary. First, install the drivers using the included CD. Then, connect the adapter to the display and the source using a VGA cable and the included USB 2.0 cable, respectively.

This USB-to-VGA converter supports high-definition video resolutions up to 1920 x 1080 (1080p) at 60 Hz and features 128 MB DDR SDRAM of memory. Compatible with 32- and 64-bit Windows 7 and later, Windows 10, as well as 32- and 64-bit Intel Mac OS X 10.8.3 and later, Mac 10.11. The adapter also works with Surface tablets running Windows 8 Pro or later.

### Features

#### Easy to Add Displays

- Extend video to a second monitor, duplicate the same video on both monitors, or make the second monitor your primary display
- Ideal for multitasking, viewing spreadsheet data, editing documents, giving presentations, watching movies and playing video games
- Add up to 6 adapters, each connected to its own USB 2.0 port, for a total of 7 displays
- No external power supply necessary
- No need to reboot system after adding or removing a monitor

**Vibrant, Superior Video Quality**

### Highlights

- Extend video to a second display or duplicate one video on both
- Add up to 6 adapters to connect a total of 7 displays
- No external power supply needed
- Supports HD video resolutions up to 1920 x 1080 (1080p) @ 60 Hz
- Compatible with Windows and Mac computers
- Compatible with Ubuntu 14.04.2

### System Requirements

- Computer with USB 2.0 port
- VGA monitor
- Windows 7 or later, Windows 10 (32- or 64-bit), Intel Mac OS X 10.8.3 or later, Mac 10.11 (32- or 64-bit) or Surface tablet running non-RT Windows 8 or 8.1

### Package Includes

- U244-001-VGA-R USB 2.0 to VGA Dual-Monitor Adapter
- USB cable, 3 ft.
- Quick Start Guide
- Driver CD with Owner's Manual



- Supports high-definition video resolutions up to 1920 x 1080 (1080p) @ 60 Hz
- Features 128 MB DDR SDRAM of memory
- Uses DisplayLink DL-165 chipset
- Resumes automatically from hibernation and suspend modes

**PC and Mac Compatible**

- Works with 32- and 64-bit Windows 7 and later, Windows 10
- Works with 32- and 64-bit Intel Mac OS X 10.8.3 and later, Mac 10.11
- Works with Surface tablets running Windows 8 Pro or later

## Specifications

OVERVIEW	
UPC Code	037332165107
Technology	USB 2.0 (High Speed); VGA/SVGA
VIDEO	
Max Supported Video Resolution	1920 x 1080 (1080p) @60Hz
INPUT	
Bus Powered	Yes
PHYSICAL	
Material of Construction	ABS
Color	Black
Shipping Dimensions (hwd / cm)	21.59 x 15.24 x 5.72
Shipping Dimensions (hwd / in.)	8.50 x 6.00 x 2.25
Shipping Weight (kg)	0.23
Shipping Weight (lbs.)	0.50
Unit Dimensions (hwd / in.)	0.71 x 3.3 x 2.2
Unit Packaging Type	Clamshell
Unit Weight (lbs.)	0.12
Unit Weight (kg)	0.05
ENVIRONMENTAL	
Operating Temperature Range	50 to 104 F (10 to 40 C)
Storage Temperature Range	-4 to 158 F (-20 to 70 C)
Relative Humidity	0% to 85% RH, Non-Condensing



<b>CONNECTIONS</b>	
Number of Ports	1
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	HD15 (FEMALE)
Connector Plating	Nickel
<b>FEATURES &amp; SPECIFICATIONS</b>	
USB Specification	USB 2.0 (up to 480 Mbps)
Driver Required	Yes
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2022 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>