

USB 2.0 2.5in IDE ATA External Hard Drive Enclosure

MODEL NUMBER: **U256-025**



Highlights

- Lightweight, compact design ideal for portable storage
- Fits standard 2.5 in. IDE / ATA drives
- Windows and Macintosh compatible, Plug and Play

System Requirements

- Pentium 266 MHz or higher
- 64 MB RAM
- Windows 98SE/Me/2000/XP/Vista/7 or MAC OS 9.0 and above

Description

Tripp Lite's U256-025 is an inexpensive way to create an external USB storage drive, ideal for laptop / notebook users. Simply insert any manufacturers ATA / IDE 2.5" hard drive (not supplied) into the rugged aluminum case, and plug the Included USB cable into the a computer or hub USB port (2 ports required for data and power). At only 4.75"L x 3.25"W x 0.5"H, the U256-025 travels easily, and includes a protective travel bag. External drives are great for storing large files like photos, music, movies, etc. Compatible with Windows 98SE / Me / 2000 / XP / Vista / Win7 or MAC OS 9.0 and above. Supports USB 2.0 data transfer rates up to 480Mbps.

Features

- Lightweight, compact design ideal for portable storage
- Fits standard 2.5 in. IDE / ATA drives (not supplied)
- Windows and Macintosh compatible
- Windows 98SE/Me/2000/XP/Vista/7 or MAC OS 9.0 and above
- 4.75"L x 3.25"W x 0.5"H
- 44-pin IDE internal connection
- Hi-Speed USB 2.0 mini B external connection
- USB cable, A-type male x 2 to mini B male, 4 ft. (1.2 m)

Specifications

OVERVIEW	
UPC Code	037332151926
Drives Supported	2.5" IDE / ATA
Technology	USB 2.0 (High Speed)
CONNECTIONS	



Powering Business Worldwide



Side A - Connector 1	USB A (MALE)
Side B - Connector 1	40 POS. SOCKET (FEMALE)
PHYSICAL	
Color	Silver
Material of Construction	Aluminum
Shipping Dimensions (hwd / in.)	1.90 x 8.10 x 6.10
Shipping Dimensions (hwd / cm)	4.83 x 20.57 x 15.49
Shipping Weight (lbs.)	0.55
Shipping Weight (kg)	0.25
ENVIRONMENTAL	
Operating Temperature Range	32 to 104 F (0 to 40 C)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.