

USB 2.0 2.5in SATA External Hard Drive Enclosure

MODEL NUMBER: **U257-025**



Description

Tripp Lites U257-025 is an inexpensive way to create an external USB storage drive, ideal for laptop / notebook users. Simply insert any manufacturers SATA 2.5" hard drive (not supplied) into the rugged metal/ABS case, and plug the built in USB cable into the a computer or hub USB port. Unit is Plug-n-Play...no software to load. At only 5.25"L x 3.25"W x .5"H, the U257-025 travels easily...great for storing large files like photos, music, movies, etc. Compatible with Windows 2000, XP, Vista, Win7, and Mac OS 9.2 and above. Supports USB 2.0 data transfer rates up to 480Mbps.

Features

- Lightweight, compact design ideal for portable storage
- Fits standard 2.5 in. SATA drives (not supplied)
- Windows and Macintosh compatible, Plug and Play
- Built in, self-storing USB "A" attachment cable (1.25" long)
- Windows 2000, XP, Vista, Win7, and Mac OS 9.2 and above compatible
- Power / Activity LED indicator
- Secure cover lock / unlock switch
- Limited Lifetime Warranty

Specifications

OVERVIEW	
UPC Code	037332151919
Drives Supported	2.5" SATA
Technology	SATA/eSATA; USB 2.0 (High Speed)
INPUT	
Input Plug Type	USB A (Male)

Highlights

- Lightweight, compact design ideal for portable storage
- Fits standard 2.5 in. SATA drives
- Windows and Macintosh compatible, Plug and Play

System Requirements

- Available USB type-A port (computer or hub)
- Win 2000, XP, Vista, Win7, MAC OS 9.2 or above
- If you are connecting the U257-025 to a computer running Mac OS8.6, you will need to download and install the USB Mass Storage Support 1.3.5 software from www.apple.com/support.

Package Includes

- U257-025 External Enclosure
- Owner's manual



Powering Business Worldwide



CONNECTIONS	
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	22 PIN SATA + POWER (FEMALE)
PHYSICAL	
Color	Black
Material of Construction	Metal, ABS
Housing Color	Black
Shipping Dimensions (hwd / in.)	1.60 x 7.30 x 5.30
Shipping Dimensions (hwd / cm)	4.06 x 18.54 x 13.46
Shipping Weight (lbs.)	0.33
Shipping Weight (kg)	0.15
Unit Weight (lbs.)	.16
Unit Weight (kg)	0.07
ENVIRONMENTAL	
Operating Temperature Range	32 to 104 F (0 to 40 C)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.