

## Wireless Apple CarPlay Adapter for Vehicles, Apple iPhone Compatible, Black

MODEL NUMBER: U264-001-APL



Creates a wireless connection between a vehicle and an Apple iPhone to operate Apple CarPlay functions.

### Features

#### Enhance Your Driving Experience with a Wireless CarPlay Experience

The U264-001-APL adapter provides a wireless connection to Apple CarPlay in vehicles that require a wired CarPlay connection. It is compatible with Apple iPhone 6 or later models that are on iOS 10 and above. Not only does this adapter reduce cable clutter in your vehicle, it also allows you to operate CarPlay functions such as music and podcast control, answer calls and texts via voice-to-text, navigate via Apple Maps and make voice commands through Siri. An included USB-A to USB-C adapter lets you connect to either port in a vehicle.

#### Easy Installation Allows for Quick Setup and Recurring Use

An ideal tool for travelers, particularly sales professionals always on the go, this adapter uses a combination of Bluetooth and Wi-Fi to establish a pairing between the phone and the vehicle and switches to Wi-Fi to maintain the wireless connection. Once the initial connection is established, the U264-001-APL will instantly reconnect to the phone moving forward. A green LED indicates that a connection is established. **Note:** The U264-001-APL is only compatible with vehicles that require a wired CarPlay connection. Vehicles with support for a Bluetooth connection to CarPlay do not require this device.

## Specifications

OVERVIEW	
UPC Code	037332292308
Product Type	USB Wireless Apple Carplay Adapter
Device Compatibility	Phone
Technology	USB; Wireless
Country/Region	Global
Host Connector	(1) USB A (MALE)

### Highlights

- Recommended for daily travel use, especially sales pros who are always on the go
- Reduces cable clutter in your vehicle while enabling music, navigation, Siri control and more
- Included USB adapter allows connection with your vehicle's USB-A or USB-C port
- Compatible with Apple iPhone 6 or later models that are on iOS 10 and above
- Plug-and-play operation with no software required for easy, immediate installation

### System Requirements

- Vehicle with support for wired Apple CarPlay (**Note:** Vehicles that support Apple CarPlay via a Bluetooth connection do not require this device)
- Apple iPhone 6 or later model on iOS 10 or above

### Package Includes

- U264-001-APL Wireless Apple CarPlay Adapter
- USB-A to USB-C adapter
- Installation instructions



Powering Business Worldwide

TRIPP LITE  
SERIES

INPUT	
Built-In Cable Length (ft.)	0.33
Built-In Cable Length (in.)	4
Built-In Cable Length (cm)	10
Bus Powered	Yes
POWER	
Power Source Type	Bus
CONNECTIONS	
Number of Ports	0
Side A - Connector 1	USB A (MALE)
Connector Plating	Nickel
Connector Style	Straight
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	(1) Connection LED: Turns blue when initially powered on before turning to green (flashes when attempting to connect to iPhone; solid when connection is established).
PHYSICAL	
Color	Black
Material of Construction	MAIN BODY: TEMPERED GLASS AND ALUMINUM; PCB
Cable Jacket Color	Black
Cable Jacket Material	TPE
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	3.3MM
Wire Gauge (AWG)	28
Cable Length (ft.)	0.5
Cable Length (m)	0.15
Cable Length (in.)	6
Total Number of Ports	0
Shipping Dimensions (hwd / in.)	1.06 x 5.71 x 2.95
Shipping Dimensions (hwd / cm)	2.69 x 14.50 x 7.49
Shipping Weight (lbs.)	0.22
Shipping Weight (kg)	0.10
Unit Dimensions (hwd / in.)	0.550 x 2.320 x 1.570
Unit Dimensions (hwd / cm)	4 x 0.9 x 6



Powering Business Worldwide

TRIPP LITE  
SERIES

Unit Dimensions (hwd / mm)	40 x 9.2 x 60
Unit Packaging Type	Box
Unit Weight (lbs.)	0.15
Unit Weight (kg)	0.07
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32° to 122°F (0 to 50°C)
Storage Temperature Range	-4° to 158°F (-20° to 70°C)
Operating Humidity Range	10% to 90% RH, Non-Condensing
Storage Humidity Range	0% to 95% RH, Non-Condensing
<b>FEATURES &amp; SPECIFICATIONS</b>	
Over Current Protection	N
USB Hub Ports	No
Number of USB Hub Ports	0
Driver Required	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	EN 55032; EN 55035; ICES (Canada)
Product Compliance	CE (Europe); FCC Part 15 Class B (USA); REACH; RoHS; UKCA; WEEE
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.