

USB Tablet / Phone Car Charger, 5V 2.4A / 12W

MODEL NUMBER: U280-001-C2



Charge your Tablet and Phone in your car.

Description

Tripp Lite's 2.4Amp USB Car Charger allows you to quickly and safely charge a USB-powered device and is ideal for ultra-fast charging devices such as iPad (including iPad Mini), other tablets, and cellular phones. This high-quality and ultra-compact charger works with any standard in-vehicle power outlet and features a translucent ring around the USB port that glows blue to indicate power is being passed through to your device. It is a handy tool to keep your devices fully-charged and ready to use while you are on-the-go.

Features

- High-speed 2.4A USB port for charging devices, including iPads, tablets, eReaders, smartphone's and more
- Works with any 12V DC auto lighter socket
- Use your existing USB cables to charge all devices
- 5V 2.4A USB port

Specifications

OVERVIEW	
UPC Code	037332184276
Product Type	Car Charger
Charging Form Factor	Direct Plug-In
Device Compatibility	Phone; Tablet; Amazon Kindle
Technology	USB
INPUT	
Nominal Input Voltage(s) Supported	12V DC

Highlights

- Quickly charges a Tablet or Phone with up to 2.4A of power
- 5V 2.4A USB port

System Requirements

- Automobile 12V DC Lighter Socket

Package Includes

- 2.4A Single USB Car Charger



Input Connection Type	Automatic Vehicle Cigarette Lighter
Input Plug Type	Car Auxiliary Power Outlet
OUTPUT	
Output Watt Capacity (Watts)	12
Overload Protection	Yes
CHARGING	
Number of Charging Ports	1
Total Charging Amps	1.4A
Total Charging Watts	12
Charging Method	USB
Charging Port Type	USB A (FEMALE)
Charging Ports Details	USB-A: 5V 2.4A (12W)
Charging Ports / Amps	(1) 2.4A
Compatible Devices	Laptop; Smartphone; Tablet
PHYSICAL	
Color	White
Shipping Dimensions (hwd / in.)	1.00 x 4.10 x 6.10
Shipping Dimensions (hwd / cm)	2.54 x 10.41 x 15.49
Shipping Weight (lbs.)	0.06
Shipping Weight (kg)	0.03
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
ENVIRONMENTAL	
Operating Temperature Range	32 to 104 F (0 to 40 C)
Storage Temperature Range	-40 to 176 F (-40 to 80 C)
Operating Humidity Range	20 to 90% RH, Non-Condensing
Storage Humidity Range	5 to 95% RH, Non-Condensing
CONNECTIONS	
Number of Ports	1
Side A - Connector 1	Car Cigarette Lighter
Side B - Connector 1	USB A (FEMALE)
FEATURES & SPECIFICATIONS	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Overcurrent Protection	Yes
Overvoltage Protection	Yes
GaN Technology	No
STANDARDS & COMPLIANCE	
Product Compliance	CE (Europe); FCC (USA); RoHS
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2022 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>