

10-Port USB Charging Station - 5V 21A / 105W USB Charger Output

MODEL NUMBER: **U280-010**



Highlights

- Charges up to 10 tablets, phones or other mobile devices
- Provides up to 5V, 2.1A per port to 10 ports simultaneously
- An individual port can provide a maximum of 5V, 2.4A of power
- All ten ports support USB Battery Charging (BC) specification v1.2
- Charge your devices without the need to connect to a computer

System Requirements

- A tablet, phone or other mobile device

Package Includes

- U280-010 10-Port USB Charger
- C13 to 5-15P Power Cord
- Rubber Feet
- Owner's Manual

Description

For the battery-intensive mobile devices of today, a standard USB hub is not sufficient for charging. Tripp Lite's U280-010 10-Port USB Charger is the solution, allowing you to charge up to 10 tablets, phones or other mobile devices all at the same time. Up to 5V, 2.4A (12 Watts) of power is provided to each port, perfect for charging the most power hungry devices such as the Apple iPad. With a maximum of 105W, you can provide up to 5V, 2.1A per port simultaneously. Each port also supports USB Battery Charging (BC) specification v1.2. So whether you're at home or in the office, you no longer need to go looking for an available outlet or unplug one device to charge the other, the U280-010 provides you with the ports and power you need. Features over-heating, over-current, and over-charging (stops charging when device battery is full) protection. Includes an internal, dual-voltage (100-240V) power supply - no bulky external power supply required.

Features

- Charges up to 10 tablets, phones or other mobile devices
- Provides up to 5V, 2.1A per port to 10 ports simultaneously
- An individual port can provide a maximum of 5V, 2.4A of power
- Complies with USB Battery Charging (BC) specification v1.2
- Features over-heating, over-current, and over-charging (stops charging when device battery is full) protection
- Charge your devices without the need to connect to a computer
- Includes an internal, dual-voltage (100-240V) power supply - no bulky external power supply required

Specifications

OVERVIEW	
UPC Code	037332188199



Product Type	Charging Station
Charging Form Factor	Charging Hub
Device Compatibility	Phone; Tablet; Amazon Kindle
Technology	USB
INPUT	
Nominal Input Voltage(s) Supported	120V AC; 230V AC
Plug Type	C13 to NEMA 5-15P
Voltage Compatibility (VAC)	100; 110; 120; 125; 127; 200; 208; 220; 230; 240
Input Frequency	50/60Hz
Input Plug Type	NEMA 5-15P
Input Current	120V (1.4A) / 230V (0.7A)
OUTPUT	
Output Capacity	5V 21A
Overload Protection	Yes
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Blue (Power)
CHARGING	
Charging Ports / Amps	(10) 2.4A
Number of Charging Ports	10
Total Charging Amps	21A
Charging Method	USB
Total Charging Watts	105
Charging Ports Detail	USB-A: 5V/2.1A
Charging Port Type	(10) USB A (FEMALE)
Charging Method Detail	5V - 1.5A (7W)
PHYSICAL	
Color	Black
Material of Construction	Polycarbonate
Shipping Dimensions (hwd / cm)	5.59 x 29.97 x 15.75
Shipping Dimensions (hwd / in.)	2.20 x 11.80 x 6.20
Shipping Weight (kg)	0.95
Shipping Weight (lbs.)	2.10



Unit Dimensions (hwd / cm)	4.8 x 17.5 x 13
Unit Dimensions (hwd / in.)	1.9 x 6.9 x 5.1
Unit Packaging Type	Box
Unit Weight (kg)	0.57
Unit Weight (lbs.)	1.25
ENVIRONMENTAL	
Operating Temperature Range	41 to 95 F (5 to 35 C)
Storage Temperature Range	-4 to 122 F (-20 to 50 C)
Relative Humidity	5% to 90% RH, Non-Condensing
Power Consumption (Watts)	105W (Operating) 1.7W (Standby)
CONNECTIONS	
Ports	10
Side A - Connector 1	NEMA 5-15P
Side B - Connector 1	(10) USB A (FEMALE)
SPECIAL FEATURES	
Overcurrent Protection	Yes
Overvoltage Protection	Yes
GaN Technology	No
STANDARDS & COMPLIANCE	
Certifications	UL 60950-1:2007 R12.11, CAN/CSA-C22.2 No. 60950-1-07+A1:2011, IEC 60950-1, EN 55022: 2010+AC: 2011, EN55024: 2010, FCC 47 CFR Part 15 SubPartB, ANSI C63.4, RoHS, REACH
Approvals	UL Listed
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>