

## 10-Port USB Charging Station with Adjustable Storage, 12V 8A (96W) USB Charger Output

MODEL NUMBER: U280-010-ST



Charges up to 10 electronic devices, including tablets, cell phones and laptops, at the same time via USB connection. Neatly organizes the devices within its adjustable storage brackets while charging.

### Description

Whether you're at home or in the office, Tripp Lite's U280-010-ST 10-Port USB Charging Station provides plenty of ports and power to keep all your devices at 100% capacity. No more peering behind furniture to find an available outlet or unplugging one device to charge another. You can charge up to ten tablets, cell phones, laptops and other devices at the same time. It doesn't require a computer, so you can take it anywhere AC power is available.

To charge your USB devices, simply plug the included external dual-voltage (100V–240V) power supply into any NEMA 5-15R outlet, and connect your devices to the available USB ports. The charger protects against overheating, overcurrent and overcharging—in fact, it stops charging as soon as your devices' batteries are at full capacity. A front LED indicates the unit is turned on and receiving AC power.

The U280-010-ST supports USB Battery Charging (BC) specification v1.2 and delivers up to 5V, 2.4A to each port, which is perfect for charging even battery-intensive devices like the Apple® iPad®. Plus, adjustable brackets on top of the charger allow it to also act as storage, providing space to neatly organize devices while they charge. You can adjust the brackets to accommodate the number and size of the devices being charged.

### Features

**Charges Up to 10 Devices at the Same Time**Ideal for charging tablets, cell phones, laptops and other devices at home or workConnect devices to unit's USB ports for proficient chargingCharges anywhere AC power is available—no computer required

**Provides Plenty of Juice for Charging**Delivers up to 5V, 2.4A per port, enough for charging battery-intensive devices like the Apple iPadComplies with USB Battery Charging (BC) specification v1.2Protects against overheating, overcurrent and overcharging

**Also Functions as Efficient Storage**Includes 14 adjustable brackets that neatly organize devices while they chargeBrackets are adjustable to accommodate number and size of devices being charged

**Easy to Use**Included external dual-voltage (100–240V) power supply plugs into any NEMA 5-15R outletFront LED indicates when unit is turned on and receiving AC power

### Highlights

- Up to 5V, 2.4A per port for charging battery-intensive devices
- All ten ports support USB Battery Charging (BC) specification v1.2
- External dual-voltage power supply with NEMA 5-15P plug
- Protects against overheating, overcurrent and overcharging
- Includes 14 adjustable storage brackets for organizing devices
- Charges anywhere AC power is available—no computer required

### System Requirements

- For international use, the P058-006 (Europe) or P060-006 (UK) power cords can be purchased separately

### Package Includes

- 10-Port USB Charging Station
- External Power Supply with C6 Inlet (Input: 100–240V, 50/60 Hz, 2A; Max Output: 12V, 8A, 3 ft.)
- C5 to 5-15P Power Cord
- (14) Storage brackets
- Owner's manual

## Specifications



<b>OVERVIEW</b>	
UPC Code	037332190352
AC Adapter	Input: 100-240V, 50/60Hz, 2A; Output: 12V, 8A, 3 ft.
<b>OUTPUT</b>	
Charging Ports / Amps	(10) 2.4A
Output Capacity	12V 8A
Charging Method	USB
<b>INPUT</b>	
Voltage Compatibility (VAC)	100; 110; 120; 125; 127; 200; 208; 220; 230; 240
External Power Supply Input Specs (V / Hz / A)	100-240V / 50/60Hz / 2A
External Power Supply Output Specs (V / A)	12V / 8A
External Power Supply Cord Length (m.)	1
External Power Supply DC Barrel Connector Specs	OD: 5.5 x 2.5 x 10mm, Positive Pin, Negative Sleeve
External Power Supply Plug(s)	NEMA 5-15P North America
External Power Supply Certifications	CCC; CE; FCC; GS; PSE; RoHS; TUV; UL; cUL
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
LED Indicators	Blue (Power)
<b>PHYSICAL</b>	
Shipping Dimensions (hwd / in.)	3.11 x 10.59 x 6.14
Shipping Dimensions (hwd / cm)	7.90 x 26.90 x 15.60
Shipping Weight (lbs.)	2.71
Shipping Weight (kg)	1.23
Unit Packaging Type	Box
Unit Dimensions (hwd / in.)	1 x 9.4 x 4.7
Unit Dimensions (hwd / cm)	2,5 x 23,8 x 13,4
Unit Weight (lbs.)	0.57
Unit Weight (kg)	0.26
Material of Construction	PC
Color	Black
<b>ENVIRONMENTAL</b>	



Operating Temperature Range	41 to 95 F (5 to 35 C)
Storage Temperature Range	-4 to 122 F (-20 to 50 C)
Relative Humidity	20% to 80% RH, Non-Condensing
Power Consumption (Watts)	34W (Operating) 0.27W (Standby)
<b>CONNECTIONS</b>	
Ports	10
Side A - Connector 1	NEMA 5-15P
Side B - Connector 1	(10) USB A (FEMALE)
<b>FEATURES &amp; SPECIFICATIONS</b>	
Technology	USB
<b>CERTIFICATIONS</b>	
Certifications	EN 55022: 2010/AC: 2011, EN 55024: 2010, FCC Class B, RoHS, REACH
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>