

10-Port USB Charging Station with Adjustable Storage, 12V 8A (96W) USB Charger Output

MODEL NUMBER: U280-010-ST



Charges up to 10 electronic devices, including tablets, cell phones and laptops, at the same time via USB connection. Neatly organizes the devices within its adjustable storage brackets while charging.

Description

Whether you're at home or in the office, the U280-010-ST 10-Port USB Charging Station provides plenty of ports and power to keep all your devices at 100% capacity. No more peering behind furniture to find an available outlet or unplugging one device to charge another. You can charge up to ten tablets, cell phones, laptops and other devices at the same time. It doesn't require a computer, so you can take it anywhere AC power is available.

To charge your USB devices, simply plug the included external dual-voltage (100V–240V) power supply into any NEMA 5-15R outlet, and connect your devices to the available USB ports. The charger protects against overheating, overcurrent and overcharging—in fact, it stops charging as soon as your devices' batteries are at full capacity. A front LED indicates the unit is turned on and receiving AC power.

The U280-010-ST delivers up to 5V 2.4A to each port (5V 1.92A when fully loaded), which is perfect for charging even battery-intensive devices. Plus, adjustable brackets on top of the charger allow it to also act as storage, providing space to neatly organize devices while they charge. You can adjust the brackets to accommodate the number and size of the devices being charged.

Features

Charges Up to 10 Devices at the Same Time Ideal for charging tablets, cell phones, laptops and other devices at home or work. Connect devices to unit's USB ports for proficient charging. Charges anywhere AC power is available—no computer required.

Provides Plenty of Juice for Charging Delivers up to 5V, 2.4A per port, enough for charging battery-intensive devices like the Apple iPad*. Protects against overheating, overcurrent and overcharging*. When fully loaded the output per port becomes 5V/1.92A.

Also Functions as Efficient Storage Includes 14 adjustable brackets that neatly organize devices while they charge. Brackets are adjustable to accommodate number and size of devices being charged.

Easy to Use Included external dual-voltage (100–240V) power supply plugs into any NEMA 5-15R outlet. Front LED indicates when unit is turned on and receiving AC power.

Highlights

- Up to 5V, 2.4A per port for charging battery-intensive devices
- External dual-voltage power supply with NEMA 5-15P plug
- Protects against overheating, overcurrent and overcharging
- Includes 14 adjustable storage brackets for organizing devices
- Charges anywhere AC power is available—no computer required

System Requirements

- For international use, the P058-006 (Europe) or P060-006 (UK) power cords can be purchased separately

Package Includes

- 10-Port USB Charging Station
- External Power Supply with C6 Inlet (Input: 100–240V, 50/60 Hz, 2A; Max Output: 12V, 8A, 3 ft.)
- C5 to 5-15P Power Cord
- (14) Storage brackets
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332190352
Product Type	Charging Station
Charging Form Factor	Charging Hub
Device Compatibility	Phone; Tablet; Amazon Kindle
INPUT	
AC Power Adapter Plug(s)	NEMA 5-15P North America
AC Power Adapter Input Specs (V / Hz / A)	100-240V / 50/60Hz / 3A
AC Power Adapter Output Specs (V / A)	12V / 8A
AC Power Adapter Cord Length (m)	1
OUTPUT	
Overload Protection	Yes
POWER	
Power Source Type	AC Adapter
AC Adapter	100-240V, 50/60Hz, 3A; Output: 12V, 8A, 3-ft.
DC Barrel Plug	OD: 5.5 x 2.5 x 10mm, Positive Pin, Negative Sleeve
Power Consumption (Watts)	34
Power Consumption Detail	34W (Operating) 0.27W (Standby)
CONNECTIONS	
Number of Ports	10
Side A - Connector 1	NEMA 5-15P
Side B - Connector 1	(10) USB A (FEMALE)
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Blue (Power)
CHARGING	
Number of Charging Ports	10
Total Charging Amps	19.2A
Total Charging Watts	96
Charging Method	USB
Charging Method Detail	USB-A: 5V/Max 2.4A Apple Fast Charge
Charging Port Type	(10) USB A (FEMALE)

Charging Ports Details	USB-A: Up to 5V/2.4A
Charging Ports / Amps	(10) 2.4A
PHYSICAL	
Color	Black
Material of Construction	Polycarbonate
Shipping Dimensions (hwd / in.)	3.11 x 10.59 x 6.14
Shipping Dimensions (hwd / cm)	7.90 x 26.90 x 15.60
Shipping Weight (lbs.)	2.71
Shipping Weight (kg)	1.23
Unit Dimensions (hwd / in.)	0.984 x 9.370 x 5.276
Unit Dimensions (hwd / cm)	2,5 x 23,8 x 13,4
Unit Packaging Type	Box
Unit Weight (lbs.)	0.57
Unit Weight (kg)	0.26
ENVIRONMENTAL	
Operating Temperature Range	41° to 95°F (5° to 35°C)
Storage Temperature Range	-4° to 122°F (-20° to 50°C)
Relative Humidity	20% to 80% RH, Non-Condensing
FEATURES & SPECIFICATIONS	
GaN Technology	No
Overcurrent Protection	Yes
Overvoltage Protection	Yes
USB Specification	USB 2.0 (up to 480 Mbps)
IP68 Rated	No
IP20 Rated	No
STANDARDS & COMPLIANCE	
External Power Supply Certifications	CCC; CE; FCC; GS; PSE; RoHS; TUV; UL; cUL
Product Certifications	EN 55022; EN 55024
Product Compliance	RoHS; CE (Europe); REACH; FCC Part 15 Class B (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty



Powering Business Worldwide



1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.