

10-Port USB Charging Station with Adjustable Storage, 12V 8A (96W) USB Charger Output, Schuko Power Cord

MODEL NUMBER: U280-010-ST-CEE



10-port USB charger keeps electronic devices, including tablets, smartphones and laptops, at full capacity via USB connection. Neatly organizes the devices within its adjustable storage brackets while charging.

Description

Whether you're at home or in the office, Tripp Lite's U280-010-ST-CEE 10-Port USB Charging Station provides plenty of ports and power to keep all your devices at 100% capacity. No more peering behind furniture to find an available outlet or unplugging one device to charge another. You can charge up to ten tablets, smartphones, laptops and other devices at the same time. This docking station for multiple devices doesn't require a computer, so you can take it anywhere AC power is available.

To charge your USB devices, simply plug the included external dual-voltage (100V–240V) power supply into a Schuko outlet, and connect your devices to the available USB ports. The charger protects against overheating, overcurrent and overcharging—in fact, it stops charging as soon as your devices' batteries are at full capacity. A front LED indicates the unit is turned on and receiving AC power.

The 10-port USB charger supports USB Battery Charging (BC) specification v1.2 and delivers up to 5V 2.4A to each port, which is plenty for charging even battery-intensive devices. Adjustable brackets on top of the charger act as storage, providing space to neatly organize devices while they charge. You can adjust the brackets to accommodate the number and size of the devices being charged.

Features

Charges Up to 10 Devices at the Same Time Ideal for charging tablets, smartphones, laptops and other devices at home or work. Connect devices to unit's USB ports for proficient charging. Charges anywhere AC power is available—no computer required.

Provides Plenty of Juice for Charging Delivers up to 5V 2.4A per port to charge battery-intensive devices. Complies with USB Battery Charging (BC) specification v1.2. Protects against overheating, overcurrent and overcharging.

Also Functions as Efficient Storage Includes 14 adjustable brackets that neatly organize devices while they charge. Brackets are adjustable to accommodate number and size of devices being charged.

Easy to Use Included external dual-voltage (100–240V) power supply plugs into a Schuko outlet. Front LED indicates when unit is turned on and receiving AC power.

Highlights

- Up to 5V 2.4A per port for charging battery-intensive devices
- All ten ports support USB Battery Charging (BC) specification v1.2
- External dual-voltage power supply with Schuko plug
- Protects against overheating, overcurrent and overcharging
- Includes 14 adjustable storage brackets for organizing devices
- Charges anywhere AC power is available—no computer required (for 120V applications please use Tripp Lite's P013-Series cables, not included)

Package Includes

- U280-010-ST-CEE 10-Port USB Charging Station
- External Power Supply (Input: 100–240V, 50/60 Hz, 2A; Max Output: 12V 8A)
- C5 to CEE 7/7 Schuko Power Cord - 3-ft.
- (14) Storage brackets
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332205698
Product Type	Charging Station
Charging Form Factor	Charging Hub
Device Compatibility	Phone; Tablet; Amazon Kindle
INPUT	
Nominal Input Voltage(s) Supported	120V AC; 230V AC
Input Connection Type	USB-A Female
Plug Type	C5 to CEE 7/7 Schuko
Voltage Compatibility (VAC)	100; 110; 120; 125; 127; 200; 208; 220; 230; 240
Input Plug Type	CEE 7/7 Schuko
OUTPUT	
Overload Protection	Yes
POWER	
Power Source Type	AC Adapter
External Power Supply Plug(s)	CEE 7/7 Schuko
External Power Supply Input Specs (V / Hz / A)	100-240V / 50/60Hz / 3A
External Power Supply Output Specs (V / A)	12V / 8A
External Power Supply Cord Length (m.)	1
AC Adapter	Input: 100-240V, 50/60Hz, 3.0A; Output: 12V, 8A, 3-ft.
DC Barrel Plug	OD: 5.5 x 2.5 x 10mm, Positive Pin, Negative Sleeve
Power Consumption (Watts)	34
Power Consumption Detail	34W (Operating) 0.27W (Standby)
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Power (Blue)
CHARGING	
Number of Charging Ports	10
Total Charging Amps	8A
Total Charging Watts	96

Charging Method	USB
Charging Port Type	(10) USB A (FEMALE)
Charging Ports Details	USB-A: 12V/8A
Charging Ports / Amps	(10) 2.4A
Charging Method Detail	5V - 1.5A (7W)
PHYSICAL	
Color	Black
Material of Construction	Polycarbonate
Unit Dimensions (hwd / in.)	1.000 x 9.400 x 4.700
Unit Dimensions (hwd / cm)	2,5 x 23,8 x 11,8
Unit Packaging Type	Box
Unit Weight (lbs.)	0.66
Unit Weight (kg)	0.30
ENVIRONMENTAL	
Operating Temperature Range	41 to 95 F (5 to 35 C)
Storage Temperature Range	-4 to 122 F (-20 to 50 C)
Relative Humidity	20% to 80% RH, Non-Condensing
CONNECTIONS	
Number of Ports	10
Side A - Connector 1	CEE 7/7 SCHUKO PLUG
Side B - Connector 1	(10) USB A (MALE)
FEATURES & SPECIFICATIONS	
Driver Required	No
Quick Charge Compliant	No
IP68 Rated	No
Overcurrent Protection	Yes
Overvoltage Protection	Yes
GaN Technology	No
IP20 Rated	No
STANDARDS & COMPLIANCE	
External Power Supply Certifications	CE; FCC; UL; TUV; CCC; PSE; GS; RoHS
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)

WARRANTY & SUPPORT

Product Warranty Period
(Worldwide)

2-year limited warranty