

USB Car Charger - 25W PD Charging, USB-C, Black

MODEL NUMBER: **U280-C01-25-1B**



Quickly and safely charges and powers your tablet, smartphone or other compatible USB-C device from your vehicle's dashboard.

Features

USB Car Charger Safely Charges a Mobile Device While You're on the Move

This single-port USB-C car charger with Power Delivery (PD) 3.0 technology quickly and safely charges your smartphone, tablet, notebook, e-reader or power bank to ensure satisfactory battery charge when you reach your destination. The U280-C01-25-1B is compatible with Apple (including iPhone), Android (including Samsung), Windows and Amazon devices with USB-C or Thunderbolt 3 charging ports.

Plugs into the 12V DC Power Outlet in Your Vehicle

The compact charger connects to any standard 12V DC vehicle power outlet, such as the one on your dashboard. Just plug it in and connect your device's USB cable for fast, convenient mobile charging.

Specifications

OVERVIEW	
UPC Code	037332275332
Product Type	Car Charger
Charging Form Factor	Direct Plug-In
Device Compatibility	Amazon Kindle; Chromebook; Laptop; Phone; Tablet
Technology	USB
INPUT	
Nominal Input Voltage(s) Supported	12V DC
Input Connection Type	Automatic Vehicle Cigarette Lighter

Highlights

- 25W USB-C charger connects to the 12V DC power outlet in your car, truck or SUV
- Ideal for charging smartphones, tablets, e-readers and notebooks while traveling
- Prevents overheating and overcharging to shield your connected device from damage
- USB-C Power Delivery 3.0 port charges up to 4x faster than conventional USB chargers

Package Includes

U280-C01-25-1B USB Car Charger, Black



Voltage Compatibility (VAC)	100; 110; 120; 125; 127; 200; 208; 220; 230; 240
Input Plug Type	Car Auxiliary Power Outlet
OUTPUT	
Output Capacity	5V/3A, 9V/2.77A, 3.3V-5.9V/3A, 3.3-11V/2.25A
Output Watt Capacity (Watts)	25
Overload Protection	Yes
POWER	
USB Power Delivery (PD) Charging Support	Yes
USB Power Delivery (PD) Charging Specification	3.0
CHARGING	
Number of Charging Ports	1
Total Charging Amps	3A
Total Charging Watts	25
Charging Method	USB
Charging Port Type	USB C (FEMALE)
Charging Ports Details	5V 3A (15W), 9V 2.77A (25W) - PD 3.0 3.3V-5.9V 3A, 3.3V-11V 2.25A (25W) - PPS
Charging Ports / Amps	3A
Compatible Devices	Portable Speaker; Smartphone; Tablet
Charging Method Detail	USB-C PD 3.0 Charging up to 25W
PHYSICAL	
Color	White
Material of Construction	Polycarbonate
Unit Dimensions (hwd / in.)	5.560 x 2.960 x 2.640
Unit Dimensions (hwd / cm)	2.19 x 1.17 x 1.04
Unit Packaging Type	Polybag
Unit Weight (lbs.)	0.04
Unit Weight (kg)	0.02
ENVIRONMENTAL	
Operating Temperature Range	32 to 104 F (0 to 40 C)
Storage Temperature Range	-4 to 176 F (-20 to 80 C)
Operating Humidity Range	20 to 90% RH, Non-Condensing



Storage Humidity Range	5 to 90% RH, Non-Condensing
CONNECTIONS	
Number of Ports	1
Side A - Connector 1	Car Cigarette Lighter
Side B - Connector 1	USB C (FEMALE)
FEATURES & SPECIFICATIONS	
Over Current Protection	Yes
Driver Required	No
Overcurrent Protection	Yes
Overvoltage Protection	Yes
GaN Technology	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; CE (Europe); REACH; WEEE; FCC (USA)
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2022 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>