

## Dual-Port USB Car Charger, 100W Max - 2 USB-C Charging Ports, 100W PD 3.0 and PPS Charging, Black

MODEL NUMBER: U280-C02-100W



2-port car charger quickly and safely charges 2 tablets, smartphones and other USB-C devices at the same time.

### Features

#### USB Car Charger Safely Charges 2 Mobile Devices in Your Vehicle Simultaneously

This dual-port USB car charger with Power Delivery (PD) 3.0 and Programmable Power Supply (PPS) technology lets you quickly and safely charge two USB mobile devices at the same time. You and a passenger can connect your smartphones, laptops, tablets, handheld game consoles or e-readers to ensure satisfactory battery charge when you reach your destination.

#### A Combined 100W of Charging Power Feeds Your Power-Hungry Devices

When used together, the two USB-C ports support up to 100W of charging power combined (50W + 50W or 65W + 35W). Each port also individually provides up to 100W (PD 3.0: 5V 3A, 9V 3A, 15V 3A or 20V 5A; PPS: 5–20V 5A or 21V 4.75A) to a single device, keeping your larger devices, such as a USB-C laptop, at capacity. Connected devices are able to charge safely with overcurrent, overload, overvoltage and short-circuit protections.

#### Plugs into the 12V DC Power Outlet in Your Vehicle

The compact charger connects to any standard 12V DC vehicle power outlet, such as the one on your dashboard. Just plug it in, and connect your devices' USB cables for fast, convenient mobile charging. An easy-to-see blue LED indicates the charger is receiving power. The U280-C02-100W is compatible with Apple (including iPhone), Android (including Samsung), Windows and Amazon devices with USB-C or Thunderbolt 3 charging ports.

### Highlights

- 2-port USB charger connects to the 12V DC power outlet in your car, truck or SUV
- Ideal for charging smartphones, tablets, laptops and notebooks while traveling
- Maximum charging power output of 100W for either USB-C charging port
- Prevents overheating and overcharging to shield your essential device from damage
- USB-C Power Delivery 3.0 port charges up to 4x faster than conventional USB chargers

### System Requirements

- Devices with USB-C or Thunderbolt 3 charging ports
- USB-C charging cables
- Vehicle with standard 12V DC power outlet

### Package Includes

U280-C02-100W Dual-Port USB Car Charger, Black

## Specifications

OVERVIEW	
UPC Code	037332295705
Product Type	Car Charger
Charging Form Factor	Direct Plug-In



Powering Business Worldwide

TRIPP LITE  
SERIES

Efficiency	5V/9V/15V/20V 85%
Device Compatibility	Amazon Kindle; Chromebook; Laptop; Phone; Tablet
Technology	USB
<b>INPUT</b>	
Nominal Input Voltage(s) Supported	12V DC; 24V DC
Maximum Input Amps	15
Input Connection Type	Automatic Vehicle Cigarette Lighter
Input Plug Type	Car Auxiliary Power Outlet
Product Length (in.)	3
Product Length (cm.)	7.63
Product Length (ft.)	0.25
Product Length (m)	0.78
<b>OUTPUT</b>	
Output Capacity (Watts)	100
Output (Watts)	100W Max
Overload Protection	Yes
<b>POWER</b>	
Power Consumption (Watts)	100.00
USB Power Delivery (PD) Charging Support	Yes
USB Power Delivery (PD) Charging Specification	100W; 20V/5A; 3.0
<b>CONNECTIONS</b>	
Number of Ports	2
Side A - Connector 1	Car Cigarette Lighter
Side B - Connector 1	(2) USB C (FEMALE)
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
LED Indicators	Blue (Power)
<b>CHARGING</b>	
Number of Charging Ports	2
Total Charging Amps	5
Total Charging Watts	100
Charging Method	USB



Powering Business Worldwide

TRIPP LITE  
SERIES

Charging Method Detail	USB-C PD + PPS Charging up to 100W
Charging Port Type	(2) USB C (FEMALE)
Charging Ports Details	SINGLE OUTPUT: USB-C1/C2: 5V 3A, 9V 3A, 15V 3A, 20V 5A (100W) - PD 3.0; 5-21V 5A (100W) - PPS DUAL OUTPUT: USB-C1/C2+C2/C1: 50W + 50W OR 65W +35W
Charging Ports / Amps	3A; 5A
Magnetic Charging	No
Wireless Charging	No
Overcharge Protection	Yes
Compatible Devices	Portable Speaker; Smartphone; Tablet
<b>PHYSICAL</b>	
Color	Black
Material of Construction	PC (Plastic)
Charging Station Form Factor	Direct Plug-In
Unit Dimensions (hwd / in.)	1.340 x 2.560 x 1.370
Unit Dimensions (hwd / cm)	7.63 x 3.13
Unit Packaging Type	Polybag
Unit Weight (lbs.)	0.15
Unit Weight (kg)	0.07
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32° to 95°F (0° to 35°C)
Storage Temperature Range	-4° to 185°F (-20° to 85°C)
Operating Humidity Range	20 to 90% RH, Non-Condensing
Storage Humidity Range	5 to 95% RH, Non-Condensing
<b>INPUT TRANSFORMER</b>	
Input Voltage	12V to 24V
<b>FEATURES &amp; SPECIFICATIONS</b>	
GaN Technology	No
Overcurrent Protection	Yes
Overvoltage Protection	Yes
Over Current Protection	Yes
Quick Charge Compliant	No
Driver Required	No
<b>STANDARDS &amp; COMPLIANCE</b>	



Powering Business Worldwide

TRIPP LITE  
SERIES

Product Compliance	RoHS; CE (Europe); REACH; WEEE; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.