

Dual-Port USB Car Charger with 39W Charging - USB-C (27W) PD 3.0, USB-A (12W), Black

MODEL NUMBER: **U280-C02-39W-1B**



2-port car charger quickly and safely charges 2 tablets, smartphones and other USB-C or USB-A devices at the same time.

Features

USB Car Charger Safely Charges 2 Mobile Devices in Your Vehicle Simultaneously This dual-port USB car charger with Power Delivery (PD) 3.0 technology lets you quickly and safely charge two USB mobile devices at the same time. You and a passenger can connect your smartphones, tablets, notebooks or power banks, to name just a few compatible devices, to ensure satisfactory battery charge when you reach your destination.

A Combined 39W of Charging Power Feeds Your Power-Hungry Devices When used together, the USB-C and USB-A ports support up to 39W of charging power. The fast-charging 27W (5V 3A or 9V 3A) USB-C PD 3.0 port keeps larger devices, such as your USB-C laptop, at capacity, while the smart-charging 12W (5V 2.4A) USB-A port reliably charges smartphones and tablets.

Plugs into the 12V DC Power Outlet in Your Vehicle The compact charger connects to any standard 12V DC vehicle power outlet, such as the one on your dashboard. Just plug it in, and connect your devices' USB cables for fast, convenient mobile charging. An easy-to-see green LED indicates the charger is receiving power. The U280-C02-39W-1B is compatible with Apple (including iPhone), Android (including Samsung), Windows and Amazon devices with USB-A, USB-C or Thunderbolt 3 charging ports.

Highlights

- 2-port USB charger connects to the 12V DC power outlet in your car, truck or SUV
- Ideal for charging smartphones, tablets, e-readers and notebooks while traveling
- Maximum charging power output of 39W: 27W USB-C and 12W USB-A
- Prevents overheating and overcharging to shield your essential device from damage
- USB-C Power Delivery 3.0 port charges up to 4x faster than conventional USB chargers

Applications

- Charge up to 2 smartphones, tablets, power banks, e-readers, notebooks or any other USB-A, USB-C or Thunderbolt 3 devices while driving to your destination

System Requirements

- Vehicle with standard 12V DC power outlet

Package Includes

- U280-C02-39W-1B Dual-Port USB Car Charger, Black

Specifications

OVERVIEW	
UPC Code	037332254085
Product Type	Car Charger
Charging Form Factor	Direct Plug-In



Device Compatibility	Phone; Tablet; Amazon Kindle; Laptop; Chromebook
Over Current Protection	Yes
INPUT	
Nominal Input Voltage(s) Supported	12V DC
Input Connection Type	Automatic Vehicle Cigarette Lighter
Input Plug Type	Car Auxiliary Power Outlet
Product Length (in.)	1.98
Product Length (cm.)	5.03
Product Length (ft.)	0.165
Product Length (m.)	0.05
OUTPUT	
Output Capacity	USB-A: 5V/2.4A; USB Type-C: 5V/3A, 9V/3A
Overload Protection	Yes
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Green (Power)
CHARGING	
Charging Ports / Amps	2.4A; 3A
Number of Charging Ports	2
Total Charging Amps	5.4A
USB Power Delivery (PD) Charging Support	Yes
Charging Method	USB
Total Charging Watts	39
USB Power Delivery (PD) Charging Specification	3.0
Charging Ports Detail	USB-C: 5V 3A (15W) or 9V 3A (27W) , PD 3.0USB-A: 5V 2.4A (12W)
Charging Port Type	USB A (FEMALE); USB C (FEMALE)
Charging Method Detail	Power Delivery 3.0
PHYSICAL	
Color	Black
Material of Construction	ABS, PVC
Unit Dimensions (hwd / cm)	1.95 x 5.05 x 3.25
Unit Dimensions (hwd / in.)	0.77 x 1.99 x 1.28



Unit Packaging Type	Polybag
Unit Weight (kg)	0.03
Unit Weight (lbs.)	0.057
ENVIRONMENTAL	
Operating Temperature Range	32 to 86°F (0 to 30°C)
Storage Temperature Range	-4 to 140°F (-20 to 60°C)
Operating Humidity Range	30% to 90% RH
Storage Humidity Range	10% to 90% RH
CONNECTIONS	
Ports	2
Side A - Connector 1	Car Cigarette Lighter
Side B - Connector 1	USB A (FEMALE)
Side B - Connector 2	USB Type-C (FEMALE)
FEATURES & SPECIFICATIONS	
Quick Charge Compliant	3.0
Technology	USB
SPECIAL FEATURES	
Overcurrent Protection	Yes
Overvoltage Protection	Yes
GaN Technology	No
STANDARDS & COMPLIANCE	
Certifications	CE, FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>