

Dual-Port USB Car Charger for Tablets and Cell Phones, 5V 4.8A (24W)

MODEL NUMBER: **U280-C02-S2**



Auto-sensing USB ports allow you to charge 2 mobile devices, such as a tablet and cell phone, in your vehicle at the same time.

Description

The U280-C02-S2 Dual-Port USB Car Charger lets you quickly and safely charge two USB-powered mobile devices in your vehicle at the same time. You and your passenger can connect your cell phones simultaneously to ensure full charges when you reach your destination. Also recommended for tablets, MP3 players and other USB devices, the U280-C02-S2 features two 5V 2.4A USB ports. The auto-sensing ports automatically adjust to the appropriate power level and platform, whether your device is an Apple, Android or other. This ultra-compact charger works with any standard 12V DC vehicle power outlet.

Features

Charge 2 Mobile Devices in Your Vehicle at the Same Time

- Recommended for cell phones, tablets, e-readers and MP3 players
- Each USB port supports up to 5V 2.4A
- Auto-sensing ports adjust to appropriate power level and platform (Apple, Android, etc.)
- Works with any standard 12V DC vehicle power outlet

Specifications

OVERVIEW	
UPC Code	037332196316
OUTPUT	
Charging Ports / Amps	(2) 2.4A

Highlights

- Recommended for cell phones, tablets, e-readers and MP3 players
- Each USB port supports up to 5V 2.4A
- Auto-sensing ports adjust to appropriate power level
- Compatible with Apple, Android and other platforms
- Works with any standard 12V DC vehicle power outlet

Package Includes

- U280-C02-S2 Dual-Port USB Car Charger for Tablets and Cell Phones, 5V 4.8A (24W)



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Output Capacity	24W
Charging Method	USB
PHYSICAL	
Shipping Dimensions (hwd / in.)	0.50 x 3.20 x 4.40
Shipping Dimensions (hwd / cm)	1.27 x 8.13 x 11.18
Shipping Weight (lbs.)	0.07
Shipping Weight (kg)	0.03
Color	White
ENVIRONMENTAL	
Operating Temperature Range	32 to 104 F (0 to 40 C)
Storage Temperature Range	-4 to 140 F (-20 to 60 C)
Operating Humidity Range	30% to 90% RH, Non-Condensing
Storage Humidity Range	10% to 90% RH, Non-Condensing
CONNECTIONS	
Side A - Connector 1	Automobile Cigarette Lighter Outlet
Side B - Connector 1	(2) USB A (FEMALE)
FEATURES & SPECIFICATIONS	
Technology	USB
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>